

FPC 40/60/13 7035

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



Medium-sized polycarbonate enclosures

The FPC series of enclosures is the next generation of the MPC series. Exhibiting the same material properties, the FPC series has an even wider range of accessories and hence extends the number of potential applications.

Features:

- 6 sizes in 2 versions
- Grey or transparent cover
- Cover with lead-seal holes
- Fixing holes outside the sealed area
- Thread for fitting to terminal rails, mounting plates and PCBs
- Comprehensive accessories Weidmüller can manufacture and supply the enclosures to match customer specifications, fitted with all necessary terminals and cable glands.

General ordering data

Version	FPC (polycarbonate empty enclosure), Empty enclosure, Height: 400 mm, Width: 600 mm, Depth: 132 mm, Basic material: Polycarbonate, untreated, Light Grey
Order No.	9535810000
Type	FPC 40/60/13 7035
GTIN (EAN)	4032248009886
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	132 mm	Depth (inches)	5.1968 inch
Height	400 mm	Height (inches)	15.748 inch
Width	600 mm	Width (inches)	23.622 inch
Net weight	3964 g		

Temperatures

Operating temperature	-50 °C...130 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Cable glands, right

M25	12	M63	3
M16	30	M40	4
M50	4	M32	5
M20	18	M12	56

Cable glands, top/bottom

M20	24	M12	76
M63	4	M40	6
M32	6	M25	16
M50	4	M16	42

Certificate numbers enclosure

Declaration of Conformity No. (DoC LVD)	DE PS2420 220224 003ISS00
---	------------------------------

General information

Material thickness	3.5 mm	Operating temperature, max.	130 °C
Operating temperature, min.	-50 °C	Lid attachment	4 polyamide crosshead screws
Surface finish	untreated	Impact resistance	IK08
Protection degree	IP66, IP67	Basic material	Polycarbonate
Seal material	Polyurethane	Torque for lid screws	0.8 Nm
Integral fixing	thanks to self-tapping screws	Enclosure attachment	Holes 7.5 mm
Number of lid screws	6	Access opening: width	595.5 mm
Flange plate	No	Lid	Yes
Access opening: height	396.5 mm	Areas of use	Building systems and technology, Transportation, Packaging industry, Machine construction

Technical data

horizontal assembly


Number of DIN rails and terminals (10 mm ² , horizontal)	2x49	WDU 16 / ZDU 16	2x41
WDU 2,5 / ZDU 2,5 / IDU 2,5	2x97	WDU 35 / ZDU 35	2x31
WDU 4 / ZDU 4	2x81	WDU 6 / ZDU 6	2x61

vertical assembly

WDU 10 / ZDU 10	5x30	WDU 16 / ZDU 16	5x25
WDU 2,5 / ZDU 2,5 / IDU 2,5	5x59	WDU 35 / ZDU 35	5x19
WDU 4 / ZDU 4	5x49	WDU 6 / ZDU 6	5x37

Classifications

ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		



FPC 40/60/13 7035

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

Accessories

www.weidmueller.com

Ventilation plugs - DAE



In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Type	DAE M12 PA LONG	Version
Order No.	1868570000	DAE (ventilation element), Compensating element, straight, M 12, 10
GTIN (EAN)	4032248440429	mm, IP66, IP68, IP69K, Polyamide 6
Qty.	10 ST	
Type	DAE M12 SS	Version
Order No.	1868550000	DAE (ventilation element), Compensating element, straight, M 12, 10
GTIN (EAN)	4032248440405	mm, IP66, IP68, IP69K, Stainless steel 1.4305 (303)
Qty.	10 ST	

Earthing stud



Earthing bolts to exchange as a complete component in two versions – brass and stainless steel.

General ordering data

Type	PEBZ M6 S4 SET	Version
Order No.	1283430000	Klippon POK (polyester empty enclosure), Earthing stud,
GTIN (EAN)	4050118073607	Miscellaneous, Height: 12.3 mm, Width: 12.3 mm, Depth: 42 mm,
Qty.	1 ST	Basic material: Stainless steel 1.4404 (316L)
Type	PEBZ M6 BR SET	Version
Order No.	1277250000	Klippon POK (polyester empty enclosure), Earthing stud,
GTIN (EAN)	4050118067149	Miscellaneous, Height: 12.3 mm, Width: 12.3 mm, Depth: 42 mm,
Qty.	1 ST	Basic material: Brass
Type	PEBZ M10 S4 SET	Version
Order No.	1283440000	Klippon POK (polyester empty enclosure), Earthing stud,
GTIN (EAN)	4050118073362	Miscellaneous, Height: 21 mm, Width: 21 mm, Depth: 48.7 mm,
Qty.	1 ST	Basic material: Stainless steel 1.4404 (316L)

Klippon® POK earthing stud



The Klippon® POK enclosure range is made from a high-quality glass fibre reinforced polyester and is ideal for applications and environments where corrosion resistance, impact resistance and a high IP protection class are a requirement.

Key features of the extensive product range:

- Available in 17 sizes
- Two standard finishes (colours): grey (similar to RAL 7001 for industrial use) and black (similar to RAL 9011 for harsh environments, Ex)
- Cover with stainless steel screws in cross-head / slotted design
- Moulded gasket made of silicone or chloroprene
- Fixing holes outside the sealed area to ensure high ingress protection of IP66
- Impact resistance up to 7 Joules
- Mounting directly in the enclosure or using an internal mounting plate
- Direct wall mounting possible using fixing holes or mounting feet
- Fastening thread to attach mounting rails and plates
- Up to E60 fire rating dependent on the configuration
- Weidmüller can manufacture and supply this enclosure to match customer specifications - fitted with all necessary terminals and cable glands.

General ordering data

Type	PEBZ M10 BR SET	Version
Order No.	1277220000	Klippon POK (polyester empty enclosure), Earthing stud,
GTIN (EAN)	4050118067019	Miscellaneous, Height: 21 mm, Width: 21 mm, Depth: 48.7 mm,
Qty.	1 ST	Basic material: Brass

Hinge



MPC series, hinges, set of 2

General ordering data

Type	HG FPC	Version
Order No.	9535990000	FPC (polycarbonate empty enclosure), External joint, Hinge, Height:
GTIN (EAN)	4032248009701	40 mm, Width: 50 mm, Depth: 16.5 mm, Basic material: Plastic, Light
Qty.	1 ST	Grey

FPC 40/60/13 7035

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

External fixing lugs



External attachment lugs 4-part set

General ordering data

Type	MF FPC	Version
Order No.	9536040000	FPC (polycarbonate empty enclosure), Mounting foot, Fixing lugs,
GTIN (EAN)	4032248009442	Height: 40 mm, Width: 19 mm, Depth: 35.5 mm, Basic material:
Qty.	1 ST	Polyamide, Polyamide 66, Light Grey

FPC

Mounting plates, 1.5 mm sheet steel, galvanised



General ordering data

Type	MP FPC 40/60	Version
Order No.	9535980000	FPC (polycarbonate empty enclosure), Mounting plate, Mounting
GTIN (EAN)	4032248009695	plate, Height: 360 mm, Width: 560 mm, Depth: 1.5 mm, Basic
Qty.	1 ST	material: Sheet steel, galvanized, silver

TS 35

Accessories



General ordering data

Type	TS35X7.5 ST FPC 40 VER	Version
Order No.	8000037562	Rail, TS 35, TS 35 x 7.5, Width: 365 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653267	galvanized, chromium-plated
Qty.	20 ST	

FPC 40/60/13 7035

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Accessories

Type	TS35X7.5 ST FPC 60 HOR	Version
Order No.	8000037563	Rail, TS 35, TS 35 x 7.5, Width: 565 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653274	galvanized, chromium-plated
Qty.	20 ST	