

MP FPC 20/40**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Mounting plates, 1.5 mm sheet steel, galvanised

General ordering data

Version	FPC (polycarbonate empty enclosure), Mounting plate, Mounting plate, Height: 160 mm, Width: 360 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanized, silver
Order No.	9535940000
Type	MP FPC 20/40
GTIN (EAN)	4032248009664
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	1.5 mm	Depth (inches)	0.0591 inch
Height	160 mm	Height (inches)	6.2992 inch
Width	360 mm	Width (inches)	14.1732 inch
Net weight	656 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Type of fixing	when screwed in	Surface finish	galvanized
Basic material	Sheet steel		

Classifications

ETIM 8.0	EC000213	ETIM 9.0	EC000213
ETIM 10.0	EC000213	ECLASS 14.0	27-40-06-39
ECLASS 15.0	27-40-06-39		

MP FPC 20/40

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

TS 35

Accessories



General ordering data

Type	TS35X7.5 ST FPC 20 VER	Version
Order No.	8000037558	Rail, TS 35, TS 35 x 7.5, Width: 165 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653229	galvanized, chromium-plated
Qty.	20 ST	

TS 15

Accessories



General ordering data

Type	TS15X5 ST FPC 20 VER	Version
Order No.	8000037604	Rail, TS 15, Width: 235 mm, without slot, Steel, galvanized,
GTIN (EAN)	4050118653168	chromium-plated
Qty.	20 ST	

TS 35

Accessories



General ordering data

Type	TS35X7.5 ST FPC 40 HOR	Version
Order No.	8000037560	Rail, TS 35, TS 35 x 7.5, Width: 365 mm, with slot, without slot, Steel,
GTIN (EAN)	4050118653243	galvanized, chromium-plated
Qty.	20 ST	