

## MP FPC 30/40



Mounting plates, 1.5 mm sheet steel, galvanised

### General ordering data

Version	FPC (polycarbonate empty enclosure), Mounting plate, Mounting plate, Height: 260 mm, Width: 360 mm, Depth: 1.5 mm, Basic material: Sheet steel, galvanised, silver
Order No.	<a href="#">9535960000</a>
Type	MP FPC 30/40
GTIN (EAN)	4032248009688
Qty.	1 items

**Technical data**

**Approvals**

ROHS	Conform
------	---------

**Dimensions and weights**

Depth	1.5 mm	Depth (inches)	0.0591 inch
Height	260 mm	Height (inches)	10.2362 inch
Width	360 mm	Width (inches)	14.1732 inch
Net weight	1040 g		

**Temperatures**

Operating temperature
-----------------------

**Environmental Product Compliance**

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

**General information**

Type of fixing	when screwed in	Surface finish	galvanized
Basic material	Sheet steel		

**Classifications**

ETIM 8.0	EC000213	ETIM 9.0	EC000213
ETIM 10.0	EC000213	ECLASS 14.0	27-40-06-39
ECLASS 15.0	27-40-06-39		

## Accessories

### TS 35

#### Accessories



#### General ordering data

Type	TS35X7.5 ST FPC 30 VER	Version	
Order No.	<a href="#">8000037561</a>	Rail, TS 35, TS 35 x 7.5, Width: 265 mm, with slot, without slot, Steel,	
GTIN (EAN)	4050118653250	galvanized, chromium-plated	
Qty.	20 ST		
Type	TS35X7.5 ST FPC 40 HOR	Version	
Order No.	<a href="#">8000037560</a>	Rail, TS 35, TS 35 x 7.5, Width: 365 mm, with slot, without slot, Steel,	
GTIN (EAN)	4050118653243	galvanized, chromium-plated	
Qty.	20 ST		