

STRIPPER COAX

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Version	Sheathing strippers
Order No.	9918030000
Type	STRIPPER COAX
GTIN (EAN)	4032248359141
Qty.	1 items

STRIPPER COAX

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	18.5 mm	Depth (inches)	0.7283 inch
Height	20.5 mm	Height (inches)	0.8071 inch
Width	97 mm	Width (inches)	3.8189 inch
Net weight	39 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Cable sheathing stripper for coaxial and PVC round cables
------------------------	-----------------------------------------------------------

Stripping tools

Cable type	Coaxial data and round cables	Max. conductor diameter	7.5 mm
Min. conductor diameter	4.8 mm	Conductor cross-section, max.	44 mm ²
Conductor cross-section, min.	18 mm ²	Workable cable	PVC cables

Classifications

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

