

## STRIPPER COAX

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm<sup>2</sup> to 5 x 2.5 mm<sup>2</sup>
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

### General ordering data

Version	Sheathing strippers
Order No.	<a href="#">9918030000</a>
Type	STRIPPER COAX
GTIN (EAN)	4032248359141
Qty.	1 items

**STRIPPER COAX**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	18.5 mm	Depth (inches)	0.7283 inch
Height	20.5 mm	Height (inches)	0.8071 inch
Width	97 mm	Width (inches)	3.8189 inch
Net weight	39 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Technical data**

Description of article	Cable sheathing stripper for coaxial and PVC round cables
------------------------	---

**Stripping tools**

Cable type	Coaxial data and round cables	Max. conductor diameter	7.5 mm
Min. conductor diameter	4.8 mm	Conductor cross-section, max.	44 mm <sup>2</sup>
Conductor cross-section, min.	18 mm <sup>2</sup>	Workable cable	PVC cables

**Classifications**

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

**STRIPPER COAX**

**Drawings**

