

STRIPPER ROUND

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm² to 5 x 2.5 mm²
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

General ordering data

Version	Sheathing strippers
Order No.	9918040000
Type	STRIPPER ROUND
GTIN (EAN)	4032248359158
Qty.	1 items

STRIPPER ROUND

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	25 mm	Depth (inches)	0.9842 inch
Height	35 mm	Height (inches)	1.378 inch
Width	125 mm	Width (inches)	4.9212 inch
Net weight	50 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

Technical data

Description of article	Junction box sheathing stripper
------------------------	---------------------------------

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Max. conductor diameter	13 mm
Min. conductor diameter	8 mm	Conductor cross-section, max.	133 mm ²
Conductor cross-section, min.	50 mm ²		

Classifications

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

STRIPPER ROUND

Drawings

