

## STRIPPER PC

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- For fast and accurate stripping of cables for damp areas ranging from 8 - 13 mm diameter, e.g. NYM cable, 3 x 1.5 mm<sup>2</sup> to 5 x 2.5 mm<sup>2</sup>
- No need to set cutting depth
- Ideal for working in junction and distribution boxes

### General ordering data

Version	Sheathing strippers
Order No.	<a href="#">9918060000</a>
Type	STRIPPER PC
GTIN (EAN)	4032248359172
Qty.	1 items

**STRIPPER PC**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	25 mm	Depth (inches)	0.9842 inch
Height	35 mm	Height (inches)	1.378 inch
Width	125 mm	Width (inches)	4.9212 inch
Net weight	44.4 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	cf06c250-ed1e-4a45-9c1b-c5c8cbf13bf0

**Technical data**

Description of article	Cable sheathing stripper for data communication lines with 5-15 mm O.D. ø
------------------------	---

**Stripping tools**

Cable type	Data cable / telecommunications and IT	Max. conductor diameter	15 mm
Min. conductor diameter	5 mm	Stripping range AWG, max.	12 AWG
Stripping range AWG, min.	24 AWG	Stripping range, min.	0.25 mm <sup>2</sup>
Conductor cross-section, max.	4 mm <sup>2</sup>	Conductor cross-section, min.	0.2 mm <sup>2</sup>

**Classifications**

ETIM 8.0	EC000163	ETIM 9.0	EC000163
ETIM 10.0	EC000163	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

