

SLICER NO 16

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- Simple, fast and accurate stripping of insulation of all conventional round cables from 4 to 37 mm²
- Knurled screw at end of handle for setting the cutting depth (setting the cutting depth prevents damage to inner conductor)

General ordering data

Version	Sheathing strippers
Order No.	9918070000
Type	SLICER NO 16
GTIN (EAN)	4032248359189
Qty.	1 items

SLICER NO 16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	35 mm	Depth (inches)	1.378 inch
Height	29 mm	Height (inches)	1.1417 inch
Width	132 mm	Width (inches)	5.1968 inch
Net weight	74 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

Technical data

Description of article	Cable cutter for conductors with 4-16 mm O.D ø
------------------------	---

Stripping tools

Cable type	Flexible and solid conductors with PVC insulation	Max. conductor diameter	16 mm
Min. conductor diameter	4 mm	Stripping range AWG, max.	6 AWG
Conductor cross-section, max.	201 mm ²		

Classifications

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		