

## SLICER NO 27

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



- Simple, fast and accurate stripping of insulation of all conventional round cables from 4 to 37 mm<sup>2</sup>
- Knurled screw at end of handle for setting the cutting depth (setting the cutting depth prevents damage to inner conductor)

### General ordering data

Version	Sheathing strippers
Order No.	<a href="#">9918080000</a>
Type	SLICER NO 27
GTIN (EAN)	4032248359196
Qty.	1 items

**SLICER NO 27**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Depth	35 mm	Depth (inches)	1.378 inch
Height	29 mm	Height (inches)	1.1417 inch
Width	132 mm	Width (inches)	5.1968 inch
Net weight	71.8 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	b28ab223-64ec-44cf-adb0-4dd6ebcae141

**Technical data**

Description of article	Cable cutter for conductors with 8-28 mm O.D ø
------------------------	------------------------------------------------

**Stripping tools**

Cable type	Flexible and solid conductors with PVC insulation	Max. conductor diameter	28 mm
Min. conductor diameter	8 mm	Stripping range AWG, max.	4 AWG
Conductor cross-section, max.	615 mm <sup>2</sup>		

**Classifications**

ETIM 8.0	EC002109	ETIM 9.0	EC002109
ETIM 10.0	EC002109	ECLASS 14.0	21-04-37-06
ECLASS 15.0	21-04-37-06		

## Accessories

### Accessories / replacement parts



- Simple, fast and accurate stripping of insulation of all conventional round cables from 4 to 37 mm<sup>2</sup>
- Knurled screw at end of handle for setting the cutting depth (setting the cutting depth prevents damage to inner conductor)

### General ordering data

Type	ZUB SLICER NO 16-35	Version	
Order No.	<a href="#">9201430000</a>	Sheathing strippers	
GTIN (EAN)	4032248430314		
Qty.	2 ST		