

## DMS MANUELL 2,0-7,0

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

### General ordering data

Version	Torque screwdriver
Order No.	<a href="#">9918380000</a>
Type	DMS MANUELL 2,0-7,0
GTIN (EAN)	4032248388349
Qty.	1 items

**DMS MANUELL 2,0-7,0**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

Width	240 mm	Width (inches)	9.4488 inch
Net weight	530 g		

**Environmental Product Compliance**

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	8a39b146-a7e9-4fe1-a2bc-f82c0bb3aeeb

**Technical data**

Description of article	Torque screwdriver, from 2.0-7.0 Nm
------------------------	-------------------------------------

**Screwing tools**

Torque setting, max.	7 Nm	Torque setting, min.	2 Nm
----------------------	------	----------------------	------

**Classifications**

ETIM 8.0	EC000149	ETIM 9.0	EC000149
ETIM 10.0	EC000149	ECLASS 14.0	21-04-50-03
ECLASS 15.0	21-04-50-03		

**Accessories**

**... Phillips crosshead**

Interchangeable bits for torque screwdriver  
 Drive output acc. to DIN 5260-PH, ISO 8764/1-PH



**General ordering data**

Type	WK K PH0	Version
Order No.	<a href="#">9918570000</a>	Screwdriver insert
GTIN (EAN)	4032248388943	
Qty.	1 ST	
Type	WK K PH1	Version
Order No.	<a href="#">9918580000</a>	Screwdriver insert
GTIN (EAN)	4032248388950	
Qty.	1 ST	
Type	WK K PH2	Version
Order No.	<a href="#">9918590000</a>	Screwdriver insert
GTIN (EAN)	4032248388967	
Qty.	1 ST	

**... Pozidriv crosshead**

Interchangeable bits for torque screwdriver  
 Drive output acc. to DIN 5260-PZ, ISO 8764/1-PZ



**General ordering data**

Type	WK K PZ0	Version
Order No.	<a href="#">9918600000</a>	Screwdriver insert
GTIN (EAN)	4032248388974	
Qty.	1 ST	
Type	WK K PZ1	Version
Order No.	<a href="#">9918610000</a>	Screwdriver insert
GTIN (EAN)	4032248388981	
Qty.	1 ST	
Type	WK K PZ2	Version
Order No.	<a href="#">9918620000</a>	Screwdriver insert
GTIN (EAN)	4032248388998	
Qty.	1 ST	

### Accessories

#### ... slotted-head screws

Interchangeable bits for torque screwdriver  
 Drive output acc. to DIN 5264, ISO 2380/1



#### General ordering data

Type	WK S 0,4X2,5	Version
Order No.	<a href="#">9918520000</a>	Screwdriver insert
GTIN (EAN)	4032248388882	
Qty.	1 ST	
Type	WK S 0,5X3,0	Version
Order No.	<a href="#">9918530000</a>	Screwdriver insert
GTIN (EAN)	4032248388899	
Qty.	1 ST	
Type	WK S 0,6X3,5	Version
Order No.	<a href="#">9918540000</a>	Screwdriver insert
GTIN (EAN)	4032248388905	
Qty.	1 ST	
Type	WK S 0,8X4,0	Version
Order No.	<a href="#">9918550000</a>	Screwdriver insert
GTIN (EAN)	4032248388912	
Qty.	1 ST	
Type	WK S 1,0X5,5	Version
Order No.	<a href="#">9918560000</a>	Screwdriver insert
GTIN (EAN)	4032248388936	
Qty.	1 ST	