



Interchangeable bits for torque screwdriver
Drive output acc. to DIN 5264, ISO 2380/1

General ordering data

Version	Screwdriver insert
Order No.	9918540000
Type	WK S 0,6X3,5
GTIN (EAN)	4032248388905
Qty.	1 items

Technical data

Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	175 mm	Width (inches)	6.8898 inch
Net weight	18.48 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

Technical data

Description of article	Interchangeable bit for slotted screws, size 0.6x3.5
------------------------	--

Screwing tools

Blade width (B)	3.5 mm	Blade thickness (A)	0.6 mm
Form	Slotted	Blade length	175 mm
Torque setting, max.	1.1 Nm		

Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-04
ECLASS 15.0	21-04-42-04		