



Interchangeable bits for torque screwdriver
Drive output acc. to DIN 5264, ISO 2380/1

General ordering data

Version	Screwdriver insert
Order No.	9918550000
Type	WK S 0,8X4,0
GTIN (EAN)	4032248388912
Qty.	1 items

Technical data

Dimensions and weights

Depth	4 mm	Depth (inches)	0.1575 inch
Height	4 mm	Height (inches)	0.1575 inch
Width	175 mm	Width (inches)	6.8898 inch
Net weight	25 g		

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	Lead 7439-92-1
SCIP	6a3438d7-aa8c-48e4-8879-adf736ca79e3

Technical data

Description of article	Interchangeable bit for slotted screws, size 0.8x4
------------------------	--

Screwing tools

Blade width (B)	4 mm	Blade thickness (A)	0.8 mm
Form	Slotted	Blade length	175 mm
Torque setting, max.	2.5 Nm		

Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-04
ECLASS 15.0	21-04-42-04		