

## WK K PZ2

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)



Interchangeable bits for torque screwdriver  
Drive output acc. to DIN 5260-PZ, ISO 8764/1-PZ

### General ordering data

|                 |                            |
|-----------------|----------------------------|
| Version         | Screwdriver insert         |
| Order No.       | <a href="#">9918620000</a> |
| Type            | WK K PZ2                   |
| GTIN (EAN)      | 4032248388998              |
| Qty.            | 1 items                    |
| Delivery status | Discontinued               |
| Last order date | 2025-09-09T00:00:00+02:00  |

**WK K PZ2**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

**Technical data**

**Dimensions and weights**

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 4 mm   | Depth (inches)  | 0.1575 inch |
| Height     | 4 mm   | Height (inches) | 0.1575 inch |
| Width      | 175 mm | Width (inches)  | 6.8898 inch |
| Net weight | 20 g   |                 |             |

**Environmental Product Compliance**

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Not affected                         |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 6a3438d7-aa8c-48e4-8879-adf736ca79e3 |

**Technical data**

|                        |   |
|------------------------|---|
| Description of article | Interchangeable bit for crosshead screws, Pozidrive, size 2 |
|------------------------|---|

**Screwing tools**

|                      |           |                       |      |
|----------------------|-----------|-----------------------|------|
| Blade width (B)      | 2 mm      | Blade thickness (A)   | 2 mm |
| Form                 | Pozidrive | Size                  | 2    |
| Blade length         | 175 mm    | Blade size, crosshead | 2    |
| Torque setting, max. | 5.5 Nm    |                       |      |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC003864    | ETIM 9.0    | EC003864    |
| ETIM 10.0   | EC003864    | ECLASS 14.0 | 21-04-42-03 |
| ECLASS 15.0 | 21-04-42-03 |             |             |

## Torque screwdriver



If you demand effective and exact work, it is essential to use the precise torque. This also guarantees high repetition accuracy.

This is the perfect job for the new Weidmüller torque screwdriver with the ergonomic grip and the unique interchangeable bit system.

- Compact and especially light design
- Torque set with special tool (supplied); an unintended, incorrect setting is ruled out.
- Ergonomic handle sizes matched to the torque range.
- Tools subjected to routine testing and provided with an ID number; 100% quality control with verification and product reference.
- Clicking sound upon reaching the set torque, clearly audible and noticeable, no unnecessary tightening.
- Interchangeable blades made from high-quality wear-resistant tool steel.
- All tools fulfil the accuracy requirements of: EN ISO 6798, BS EN 26789, ASME B107.14M
- Trigger accuracy +/- 6% of the set scale value.

## General ordering data

|            |                            |                    |
|------------|----------------------------|--------------------|
| Type       | DMS MANUELL 0,5-1,7        | Version            |
| Order No.  | <a href="#">9918370000</a> | Torque screwdriver |
| GTIN (EAN) | 4032248388332              |                    |
| Qty.       | 1 ST                       |                    |
| Type       | DMS MANUELL 2,0-7,0        | Version            |
| Order No.  | <a href="#">9918380000</a> | Torque screwdriver |
| GTIN (EAN) | 4032248388349              |                    |
| Qty.       | 1 ST                       |                    |