

CABTITE LNS M50 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Általános rendelési adatok

Változat	leválasztható ellenanya, Cabtite (cable entry system), Poliamid, üvegszál-erősítésű, mélyfekete, Magasság: 58 mm, Szélesség: 58 mm, Mélység: 7 mm, -40 °C... 120 °C
Rendelési szám	2584030000
Típus	CABTITE LNS M50 BK
GTIN (EAN)	4050118616286
Qty.	5 Darab

CABTITE LNS M50 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Műszaki adatok

Tanúsítványok

ROHS	Megfelel
------	----------

Méretek és tömegek

Mélység	7 mm	Mélység (coll)	0.2756 inch
Magasság	58 mm	Magasság (coll)	2.2835 inch
Szélesség	58 mm	Szélesség (coll)	2.2835 inch
Átmérő	67 mm	Nettó tömeg	6 g

Hőmérséklet

Üzemi hőmérséklet	-40 °C...120 °C
-------------------	-----------------

Termékek környezetvédelmi megfelelése

RoHS megfelelési állapot	Megfelel, kivétel nélkül
REACH SVHC	Nincs 0,1 tömeg% feletti SVHC

General information

Szilikon	Nem	UL 94 éghetőségi osztály	V-0
Menetemelkedés	1.5 mm	Halogén	Nem
AF 1. méret	58 mm	AF 2. méret	67 mm
Alapanyag	Poliamid, üvegszál-erősítésű	Külső menet	M 50
Menet hossza	7 mm		

Besorolások

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

CABTITE LNS M50 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Rajzok

www.weidmueller.com

Méretrajz

