

CABTITE LNS M40 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Általános rendelési adatok

| | |
|----------------|---|
| Változat | leválasztható ellenanya, Cabtite (cable entry system), Poliamid, üvegszál-erősítésű, mélyfekete, Magasság: 48 mm, Szélesség: 48 mm, Mélység: 7 mm, -40 °C... 120 °C |
| Rendelési szám | 2584050000 |
| Típus | CABTITE LNS M40 BK |
| GTIN (EAN) | 4050118616927 |
| Qty. | 5 Darab |

CABTITE LNS M40 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Műszaki adatok

Tanúsítványok

| | |
|------|----------|
| ROHS | Megfelel |
|------|----------|

Méretek és tömegek

| | | | |
|-----------|-------|------------------|-------------|
| Mélység | 7 mm | Mélység (coll) | 0.2756 inch |
| Magasság | 48 mm | Magasság (coll) | 1.8898 inch |
| Szélesség | 48 mm | Szélesség (coll) | 1.8898 inch |
| Átmérő | 55 mm | Nettó tömeg | 5.8 g |

Hőmérsékletek

| | |
|-------------------|-----------------|
| Üzemi hőmérséklet | -40 °C...120 °C |
|-------------------|-----------------|

Termékek környezetvédelmi megfelelése

| | |
|--------------------------|-------------------------------|
| RoHS megfelelési állapot | Megfelel, kivétel nélkül |
| REACH SVHC | Nincs 0,1 tömeg% feletti SVHC |

General information

| | | | |
|----------------|------------------------------|--------------------------|-------|
| Szilikon | Nem | UL 94 éghetőségi osztály | V-0 |
| Menetemelkedés | 1.5 mm | Halogén | Nem |
| AF 1. méret | 48 mm | AF 2. méret | 55 mm |
| Alapanyag | Poliamid, üvegszál-erősítésű | Külső menet | M 40 |
| Menet hossza | 7 mm | | |

Besorolások

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ETIM 10.0 | EC000940 | ECLASS 14.0 | 27-14-08-07 |
| ECLASS 15.0 | 27-14-08-07 | | |

CABTITE LNS M40 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Rajzok

www.weidmueller.com

Méretrajz

