

## HDC MPN 3.0 M

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Make your connections fit for the future With the advanced solutions from RockStar® ModuPlug Industrial applications are becoming increasingly complex. The demands being made of the connectivity used are growing at the same time. Functionality in the smallest of installation spaces, safe installation and a fast retrofitting process are just some of the product properties being called for. Not only does our RockStar® ModuPlug modular plug-in connector system meet current market requirements; it has been specially designed with the future in mind too. Using the individual modules, you combine all the necessary functions for power, signal and data transmission in a single interface. Thanks to the new variety of module sizes, you can fit more applications than ever before in one plug-in connector. The modules reduce the amount of space required and cut costs when compared with fixed-pole inserts and other modular plug-in connector systems. The sophisticated frames and modules can be installed with extreme ease and integrated into HDC enclosures with the IP65 and IP68 protection classes. You can even use the RockStar® ModuPlug to supplement existing applications without any need to make system adjustments. As an experienced Industrial Connectivity partner, Weidmüller offers ultra-modern connectivity with maximum reliability. So you can create customised solutions for future-proof connections with RockStar® too.

### Általános rendelési adatok

Változat	Pneumatikus csatlakozók, Érintkezés a szeleppel: Nem
Rendelési szám	<a href="#">2637440000</a>
Típus	HDC MPN 3.0 M
GTIN (EAN)	4050118654585
Qty.	10 Darab

## HDC MPN 3.0 M

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

### Tanúsítványok

ROHS	Megfelel
------	----------

### Méreték és tömegek

Nettó tömeg	0.29 g
-------------	--------

### Hőmérsékletek

Hőmérsékleti határérték	-40 °C ... 80 °C
-------------------------	------------------

### Termékek környezetvédelmi megfelelősége

RoHS megfelelőségi állapot	Megfelel, kivétel nélkül
REACH SVHC	Nincs 0,1 tömeg% feletti SVHC

### Pneumatikus csatlakozó

Típus	Dugó	Üzemi nyomás	≤8 bar
Tömítő belső átmérője	3 mm	Érintkezés a szeleppel	Nem

### Besorolások

ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

**HDC MPN 3.0 M**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Accessories****Pneumatikus modulok****Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**Általános rendelési adatok**

Típus	HDC MPN 3	Változat
Rendelési szám	<a href="#">2637340000</a>	Pneumatikus modul, Pólusszám: 3, Csőcsatlakozás (pneumatika), pneumatikus, Dugaszhelyek szükséges száma: 1
GTIN (EAN)	4050118765823	
Qty.	1 ST	