

HDC MBUS CT A 9.2-10.3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Comprehensive portfolio for flexible on site data cabling: from dedicated tools to Cat.#5 D coded and Cat.#6 X coded connectors, as well as robust shielding sleeves. These components enable reliable, field assembled data connections – ideal for industrial applications, quick installation, and maximum flexibility.

Dati generali per l'ordinazione

Versione	Pressing tool
N. d'ordine	2592690000
Tipo	HDC MBUS CT A 9.2-10.3
GTIN (EAN)	4050118603798
CPZ	1 Pieza

HDC MBUS CT A 9.2-10.3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Dati tecnici

Dimensioni e pesi

Lunghezza	251 mm	Lunghezza (pollici)	9.8819 inch
Peso netto	646.2 g		

Conformità ambientale del prodotto

Stato conformità RoHS	Non interessato
REACH SVHC	Lead 7439-92-1
SCIP	0c817d37-3182-4863-b78d-7f8023388f84

Dati tecnici

Versione	meccanico, con matrici intercambiabili
----------	--

Dati utensile di crimpatura

Sezione del terminale, max.	10.3 mm ²	Sezione del terminale, min.	9.2 mm ²
Tipo/profilo di crimpatura	Crimpatura esagonale		

Classificazioni

ETIM 8.0	EC000168	ETIM 9.0	EC000168
ETIM 10.0	EC000168	ECLASS 14.0	21-04-38-11
ECLASS 15.0	21-04-38-11		