

DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



一般注文データ

バージョン	太陽光発電, 負荷開閉器, 1000 V, DCバージョン, 50 A, 2 極, 手動式スイッチ, ケーブルグランド
注文番号	3123770000
種別	DC SB M 50A 2POL CG 1KV
GTIN (EAN)	4099987271981
数量	1 items

DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

技術データ

承認

ROHS 適合

寸法と重量

深さ	121.5 mm	奥行き (インチ)	4.7835 inch
高さ	165 mm	高さ (インチ)	6.4961 inch
幅	140 mm	幅 (インチ)	5.5118 inch
正味重量	621 g		

温度

周囲温度 -30 °C...50 °C

環境製品コンプライアンス

RoHS 対応状況 準拠 (免除なし)
REACH SVHC 0.1wt%を超えるSVHCは含まれていません

配送品に同梱

付属アクセサリ	製品	フォークケーブルラグ
	数量	4

一般データ

保護度合い IP65

分類

ETIM 8.0	EC000216	ETIM 9.0	EC004830
ETIM 10.0	EC004830	ECLASS 14.0	27-07-02-03
ECLASS 15.0	27-07-02-03		

入札仕様書

長体仕様

Load break switch in polyester housing.
Suitable for switching off the DC side.
Number of poles: 2
Operating current, rated value (Ie):
- according to IEC (PV1, 1000 V): 50 A
- according to IEC (PV1, 1500 V): 20 A
- according to IEC (PV2, 1000 V): 20 A
- according to IEC (PV2, 1500 V): 8 A
Rated insulation voltage (Ui):
- according to IEC: 1500 V
Suitability for use:
Main switch: Yes
Number of contacts normally open: 4

DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

技術データ

www.weidmueller.com

Number of contacts normally closed: 0
Number of switching positions: 2
Lockable: Yes
The switch is mounted using 4 screws.
Protection class (IP): 65
Polyester housing with M25 cable Gland with multiple sealing inserts for PV conductor with max. conductor cross-section: 6 mm².
Dimensions HxWxD: 165x140x121.5 mm.
Approval according to low voltage switchgear and controlgear IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)

DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

図面

