

## DC SB M 50A 4POL EVO 1 KV

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com



## 一般注文データ

バージョン	太陽光発電, スイッチ, 断路器, 1000 V, DCバージョン, 50 A, 4 極, 手動式スイッチ
注文番号	<a href="#">3123820000</a>
種別	DC SB M 50A 4POL EVO 1 KV
GTIN (EAN)	4099987272032
数量	1 items

## DC SB M 50A 4POL EVO 1 KV

Weidmüller Interface GmbH & Co. KG  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## 技術データ

## 承認

ROHS 適合

## 寸法と重量

深さ	121.5 mm	奥行き (インチ)	4.7835 inch
高さ	165 mm	高さ (インチ)	6.4961 inch
幅	140 mm	幅 (インチ)	5.5118 inch
正味重量	702 g		

## 温度

周囲温度 -30 °C...50 °C

## 環境製品コンプライアンス

RoHS 対応状況 準拠 (免除なし)  
 REACH SVHC 0.1wt%を超えるSVHCは含まれていません

## 一般データ

保護度合い IP65

## 分類

ETIM 8.0	EC000216	ETIM 9.0	EC004830
ETIM 10.0	EC004830	ECLASS 14.0	27-07-02-03
ECLASS 15.0	27-07-02-03		

## 入札仕様書

長体仕様

Load break switch in polyester housing.  
 Suitable for switching off the DC side.  
 Number of poles: 4  
 Operating current, rated value (Ie):  
 - according to IEC (PV1, 1000 V): 50 A  
 - according to IEC (PV1, 1500 V): 20 A  
 - according to IEC (PV2, 1000 V): 20 A  
 - according to IEC (PV2, 1500 V): 8 A  
 Rated insulation voltage (Ui):  
 - according to IEC: 1500 V  
 Suitability for use:  
 Main switch: Yes  
 Number of contacts normally open: 4  
 Number of contacts normally closed: 0  
 Number of switching positions: 2  
 Lockable: Yes  
 The switch is mounted using 4 screws.

**DC SB M 50A 4POL EVO 1 KV**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

技術データ

[www.weidmueller.com](http://www.weidmueller.com)

Protection class (IP): 65  
Polyester housing with  
connection via MC4-Evo  
2 connector, compatible  
with cable type TÜV 2  
Pfg 1169/08.07 / EN  
50618:2063  
Dimensions HxWxD:  
235x140x12.5 mm.  
Approval according to low  
voltage switchgear and  
controlgear IEC 60947-3,  
DIN VDE 0660 Part 107  
(EN 60947-3)

DC SB M 50A 4POL EVO 1 KV

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

図面

