

## FAD 1771-WN 2SL20 M US

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## 図に類似



移行用アダプター - PLC-5。  
組立済ケーブル付きの表側アダプターにより、PLC-5 カードから他の PLC/DCS システムまたはワイドミュラー製 u-remote モジュールへの安全な移行が可能です。

## 一般注文データ

注文番号	7940125449
種別	<a href="#">FAD 1771-WN 2SL20 M US</a>
GTIN (EAN)	4064675208877
数量	1 items

## FAD 1771-WN 2SL20 M US

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## 技術データ

## 承認

MAMID承認件数



## 寸法と重量

深さ	33 mm	奥行き (インチ)	1.2992 inch
高さ	269 mm	高さ (インチ)	10.5905 inch
幅	32 mm	幅 (インチ)	1.2598 inch
正味重量	10667.74 g		

## 温度

保管温度	-40...60 °C	動作温度	0...50 °C
------	-------------	------	-----------

## 環境製品コンプライアンス

RoHS 対応状況	準拠 (免除なし)
REACH SVHC	0.1wt%を超えるSVHCは含まれていません

## 接続データ

極数 (コントロール側)	40 極	接続 (フィールド側)	Card edge
制御側の接続	SL 3.5 ヘッダー		

## 接続データ

接続 (フィールド側)	Card edge	PLCへの接続	2 x SL 3.5/F 20pコネクタ
-------------	-----------	---------	----------------------

## 評価データ

チャンネルごとの最大電流	2 A	合計動作電流	8 A
--------------	-----	--------	-----

## 分類

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

## 絶縁協調 (EN50178)

準拠	UL 61010-1:2012, 3rd Edition, UL 61010-2-201	定格絶縁電圧	<300 V AC
サージ電圧カテゴリー	II	汚染度レベル	2
絶縁テスト電圧 AC	1.5 kV		

**FAD 1771-WN 2SL20 M US**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

図面

[www.weidmueller.com](http://www.weidmueller.com)



The diagram shows a vertical terminal block with 20 pins. The pins are arranged in two columns of 10. The left column is labeled '1' through '20' from top to bottom. The right column is labeled '21' through '30' from top to bottom. The diagram is oriented vertically on the page.