



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com



## 일반 주문 데이터

버전	태양광 발전, 스위치, 스위치 디스커넥터, 600 V AC,
	125 A, 4 폴, 수동 스위치
주문 번호	3103180000
유형	AC SB M 125A 4POL CG 06KV
GTIN (EAN)	4099987148382
수량	1 items



#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

## 기술 데이터

_	o	ı
5	ĭ	_

승인



ROHS 준수

## 치수 및 중량

깊이	142 mm	깊이 (인치)	5.5905 inch
높이	320 mm	높이 (인치)	12.5984 inch
너비	205 mm	 폭 (인치)	8.0709 inch
순중량	1773 g	<del></del>	

#### 온도

주변 온도 -25 °C...55 °C

## 일반 데이터

보호 등급 IP65

#### 부하 차단 스위치

전압 유형	AC	공칭 전압	415 V
정격 전류	125 A	 NC 접점의 접점 수	0
정격 주 활성 부하-차단전류	125 A	 결선 유형	텐션 클램프 결선
정격 단략 전류	2.1 kA	 정격 피크 내전류	2.5 kA
기계적 내구성 등급	M2 (10000)	 No 접점의 접점 수	4

## 분류

ETIM 7.0	EC000216	ETIM 8.0	EC000216
ETIM 9.0	EC004830	ETIM 10.0	EC004830
ECLASS 11.0	27-07-02-03	ECLASS 12.0	27-07-02-03
ECLASS 13.0	27-07-02-03	ECLASS 14.0	27-07-02-03
ECLASS 15.0	27-07-02-03		

## 입찰 사양 시트

긴 사양

Load break Switch in polyester housing.
Suitable for disconnection on the AC side.
Number of poles: 4
Rated operational current (le) (le):
- according to IEC (AC-21): 125 A
Rated operational voltage (Ue):
- according to IEC: 415 V
Suitability for use:
Emergency Stop Switch:
No
Main Switch: Yes Number

of contacts normally open:

4

작성 날짜 16.11.2025 09:10:07 MEZ

카탈로그 상태 / 도면 2





#### Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

# 기술 데이터

Number of contacts normally closed: 0
Number of switching positions: 2
Lockable: Yes
The switch is mounted using 4 screws.
Protection class (IP): 65
Polyester housing with knockouts for cable glands.
Dimensions HxWxD: 320x205x142 mm.
Approved according to Low-voltage Switchgear and Controlgear: IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)



Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26 D-32758 Detmold Germany

www.weidmueller.com

도면







