

MBGE ADPT, HIMA D AND Z VERSION

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

MiBridge 솔루션.

마이그레이션용 어댑터 - HIMA HiQuad.

사전 조립된 케이블이 장착된 전면 어댑터는 HIMA HiQuad 카드를 다른 PLC/DCS 시스템이나 바이트몰러의 U-리모트 모듈로 안전하게 전환할 수 있도록 합니다.

일반 주문 데이터

주문 번호	8000123146
유형	MBGE ADPT, HIMA D AND Z VERSION
GTIN (EAN)	4099986851085
수량	1 items

MBGE ADPT, HIMA D AND Z VERSION

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

기술 데이터

치수 및 중량

깊이	71.4 mm	깊이 (인치)	2.811 inch
높이	127 mm	높이 (인치)	5 inch
너비	19.9 mm	폭 (인치)	0.7835 inch
순중량	0.2 g		

온도

보관 온도	-20...70 °C	작동 온도	-20...50 °C
-------	-------------	-------	-------------

정격 데이터 UL

보관 온도 UL, 최대	70 °C	작동 온도 UL, 최소	-20 °C
작동 온도 UL, 최대	50 °C	보관 온도 UL, 최소	-20 °C
정격 전류 I 최대	20 A	정격 전압 UN	125 V

결선 데이터

폴 수(제어 측)	32극	결선(필드 측)	1756 Control Logix connector
-----------	-----	----------	------------------------------

결선 데이터

결선(필드 측)	1756 Control Logix connector	PLC에 결선	신규 PLC 단자대 또는 하드와이어드
----------	------------------------------	---------	----------------------

정격 데이터

작동 전압	125 V	채널당 최대 전류	2 A
총 작동 전류	20 A		

분류

ETIM 8.0	EC002584	ETIM 9.0	EC002584
ETIM 10.0	EC002584	ECLASS 14.0	27-33-02-92
ECLASS 15.0	27-33-02-92		

절연 조정(EN50178)

정격 절연 전압	150 V	서지 전압 범주	II
오염 심각도 수준	2	펄스 전압 테스트(1,2/50µs)	1.5 kV
절연 테스트 전압 AC	0.82 kV		

MBGE ADPT, HIMA D AND Z VERSION

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

도면

www.weidmueller.com



Small technical drawing or table showing terminal connections for MBGE ADPT, HIMA D AND Z VERSION. The drawing is oriented vertically and contains a grid of terminal numbers and their corresponding connections.