
데이터 시트

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

제품 이미지





일반 주문 데이터

버전	, 수형 헤더, THT/THR 용접 결선, 90°, Tube
주문 번호	8000166085
유형	MHS 6/04-3PM/04 H M4 T3 B T
수량	
제품 데이터	IEC: 1000 V UL:
패키징	Tube

데이터 시트

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

기술 데이터

치수 및 중량

깊이	25 mm	깊이 (인치)	0.9842 inch
높이	16.6 mm	높이 (인치)	0.6535 inch
가장 낮은 버전의 높이	13.4 mm	너비	41.625 mm
폭 (인치)	1.6388 inch		

온도

주변 온도	-50 °C...120 °C

자재 데이터

절연재	PA 9T	컬러 코드	검정
컬러 차트(유사)	RAL 9011	Moisture Level (MSL)	1
UL 94 가연성 등급	V-0	접점 기본 재질	CuMg
접점 재질	구리 합금	접점 표면	주석 도금
보관 온도, 최소	-40 °C	보관 온도, 최대	70 °C
작동 온도, 최소	-50 °C	작동 온도, 최대	125 °C

IEC 정격데이터

서지 전압 등급(오염도 II/2)에 대한 정격 전압	1000 V	서지 전압 등급(오염도 III/2)에 대한 정격 전압	160 V
서지 전압 등급(오염도 III/3)에 대한 정격 전압	160 V		

중요 참고 사항

참고 사항	• Rated current related to rated cross-section & min. No. of poles. • P on drawing = pitch • Rated data refer only to the component itself. Clearance and creepage distances to other components are to be designed in accordance with the relevant application standards. • Long term storage of the product with average temperature of 50 °C and maximum humidity 70%, 36 months

분류

ETIM 8.0	EC002637	ETIM 9.0	EC002637
ETIM 10.0	EC002637	ECLASS 14.0	27-46-03-01
ECLASS 15.0	27-46-03-01		

MHS 6/04-3PM/04 H M4 T3 B T

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

도면

제품 이미지

