

AC SB M 40A 4POL CG 06KV

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Ogólne dane zamówieniowe

Wersja	Fotowoltaika, Przełącznik, Odłącznik przełącznika, 600 V AC, 40 A, 4-biegunowe, Przełączanie ręczne
Nr zam.	3103150000
Typ	AC SB M 40A 4POL CG 06KV
GTIN (EAN)	409998714835 1
Ilość	1 szt.

AC SB M 40A 4POL CG 06KV

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Dane techniczne

Karty specyfikacji przetargowych

Długa specyfikacja	<p>Load break Switch in polyester housing. Suitable for disconnection on the AC side. Number of poles: 4 Rated operational current (Ie) (Ie): - according to IEC (AC-21): 40 A Rated operational voltage (Ue): - according to IEC: 690 V Suitability for use: Emergency Stop Switch: Yes Main Switch: Yes Number of contacts normally open: 4 Number of contacts normally closed: 0 Number of switching positions: 2 Lockable: Yes The switch is mounted using 4 screws. Protection class (IP): 65 Polyester housing with knockouts for cable glands PG 16/21. Dimensions HxWxD: 165x140x121 mm. Approved according to Low-voltage Switchgear and Controlgear: IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)</p>
--------------------	--

