

**DC SB M 50A 2POL CG 1KV****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Основные данные для заказа**

Версия	Фотоэлектрическое оборудование, Переключатель, Размыкатель, 1000 V, Версия для тока DC, 50 A, Механический переключатель
Заказ №	<a href="#">3123770000</a>
Тип	DC SB M 50A 2POL CG 1KV
GTIN (EAN)	4099987271981
Кол.	1 Штука

## DC SB M 50A 2POL CG 1KV

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Technical data

## Сертификаты

ROHS	Соответствовать
------	-----------------

## Размеры и массы

Глубина	121.5 mm	Глубина (дюймов)	4.7835 inch
Высота	165 mm	Высота (в дюймах)	6.4961 inch
Ширина	140 mm	Ширина (в дюймах)	5.5118 inch
Масса нетто	621 g		

## Температуры

Температура окружающей среды	-30 °C...50 °C
------------------------------	----------------

## Экологическое соответствие изделия

Состояние соответствия RoHS	Соответствует без исключения
REACH SVHC	Нет SVHC выше 0,1 wt%

## Входит в комплект поставки

Прилагаемые принадлежности	Артикул	Вильчатые кабельные наконечники
	Количество	4

## Общие данные

Вид защиты	IP65
------------	------

## Классификации

ETIM 8.0	EC000216	ETIM 9.0	EC004830
ETIM 10.0	EC004830	ECLASS 14.0	27-07-02-03
ECLASS 15.0	27-07-02-03		

## Тендерные спецификации

Подробная спецификация	<p>Load break switch in polyester housing. Suitable for switching off the DC side. Number of poles: 2 Operating current, rated value (Ie):</p> <ul style="list-style-type: none"> <li>- according to IEC (PV1, 1000 V): 50 A</li> <li>- according to IEC (PV1, 1500 V): 20 A</li> <li>- according to IEC (PV2, 1000 V): 20 A</li> <li>- according to IEC (PV2, 1500 V): 8 A</li> </ul> <p>Rated insulation voltage (Ui):</p> <ul style="list-style-type: none"> <li>- according to IEC: 1500 V</li> </ul> <p>Suitability for use: Main switch: Yes Number of contacts normally open: 4</p>
------------------------	--

### DC SB M 50A 2POL CG 1KV

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Technical data

[www.weidmueller.com](http://www.weidmueller.com)

Number of contacts normally closed: 0  
Number of switching positions: 2  
Lockable: Yes  
The switch is mounted using 4 screws.  
Protection class (IP): 65  
Polyester housing with M25 cable Gland with multiple sealing inserts for PV conductor with max. conductor cross-section: 6 mm<sup>2</sup>.  
Dimensions HxWxD: 165x140x121.5 mm.  
Approval according to low voltage switchgear and controlgear IEC 60947-3, DIN VDE 0660 Part 107 (EN 60947-3)

## Data sheet

**DC SB M 50A 2POL CG 1KV**

## Drawings

