

CABTITE LNS M63 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Allmänna beställningsdata

| | |
|------------|--|
| Utförande | separerbar kontramutter, Cabtite (kabelinföringssystem), Polyamid, glasfiberförstärkt, Djupsvart, Höjd: 72 mm, Bredd: 72 mm, Djup: 7 mm, -40 °C...120 °C |
| Art.nr. | 2584010000 |
| Typ | CABTITE LNS M63 BK |
| GTIN (EAN) | 4050118617245 |
| Förp. | 5 items |

CABTITE LNS M63 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Tekniska data

Godkännanden

ROHS Uppfyllelse

Mått och vikter

| | | | |
|----------|-------|-----------------|-------------|
| Djup | 7 mm | Byggdjup (tum) | 0.2756 inch |
| Höjd | 72 mm | Bygghöjd (tum) | 2.8346 inch |
| Bredd | 72 mm | Byggbredd (tum) | 2.8346 inch |
| Diameter | 83 mm | Nettovikt | 8.1 g |

Temperaturer

Drifttemperatur -40 °C...120 °C

Miljööverensstämmelse för produkt

RoHS-kompatibilitetsstatus Kompatibel utan undantag
 REACH SVHC Nej mSvHC över 0,1 viktprocent

Allmän information

| | | | |
|------------------------|------------------------------|--------------------------------|-------|
| Silikon | Nej | Brännbarhetsklass enligt UL 94 | V-0 |
| Gångstigning | 1.5 mm | Halogener | Nej |
| Nyckelbredd 1 | 72 mm | Nyckelbredd 2 | 83 mm |
| Grundläggande material | Polyamid, glasfiberförstärkt | Gånga (yttre) | M 63 |
| Gängningslängd | 7 mm | | |

Klassificeringar

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 8.0 | EC000940 | ETIM 9.0 | EC000940 |
| ETIM 10.0 | EC000940 | ECLASS 14.0 | 27-14-08-07 |
| ECLASS 15.0 | 27-14-08-07 | | |

CABTITE LNS M63 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Ritningar

www.weidmueller.com

Profilritning

