

CABTITE LNS M32 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



For metric M20 to M63 through-holes, the Cabtite cable entry system offers separable cable glands for cables with and without plugs. In case of maintenance or changes in the system, pre-assembled cables with diameters of 2 to 35 mm can be inserted quickly and safely in panels or enclosures. Reliable sealing of IP66 in accordance with DIN EN 60529 and an absolutely secure fitting (strain relief based on DIN EN 62444) is ensured by placing slotted sealing elements with a wave cut around the cable before being inserted into one of the two halves of the cable gland. The separable system ensures easy and fast installation. After inserting the sealing element, the two halves of the cable gland are simply snapped together. A locknut, which is also separable, on the inside of the panel ensures a reliable and secure hold.

Allmänna beställningsdata

Utförande	separerbar kontramutter, Cabtite (kabelinföringssystem), Polyamid, glasfiberförstärkt, Djupsvart, Höjd: 40 mm, Bredd: 40 mm, Djup: 7 mm, -40 °C...120 °C
Art.nr.	2584070000
Typ	CABTITE LNS M32 BK
GTIN (EAN)	4050118616446
Förp.	10 items

CABTITE LNS M32 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Tekniska data

Godkännanden

ROHS	Uppfyllelse
------	-------------

Mått och vikter

Djup	7 mm	Byggdjup (tum)	0.2756 inch
Höjd	40 mm	Bygghöjd (tum)	1.5748 inch
Bredd	40 mm	Byggbredd (tum)	1.5748 inch
Diameter	45 mm	Nettovikt	4.2 g

Temperaturer

Drifttemperatur	-40 °C...120 °C
-----------------	-----------------

Miljööverensstämmelse för produkt

RoHS-kompatibilitetsstatus	Kompatibel utan undantag
REACH SVHC	Nej mSvHC över 0,1 viktprocent

Allmän information

Silikon	Nej	Brännbarhetsklass enligt UL 94	V-0
Gångstigning	1.5 mm	Halogener	Nej
Nyckelbredd 1	40 mm	Nyckelbredd 2	45 mm
Grundläggande material	Polyamid, glasfiberförstärkt	Gånga (yttre)	M 32
Gängningslängd	7 mm		

Klassificeringar

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

CABTITE LNS M32 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Ritningar

www.weidmueller.com

Profilritning

