

CABTITE GI X BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The pluggable click inlays allow the frame openings to be configured as required for use with small or large sealing elements. An audible "click" confirms correct installation. This means that the Cabtite cable entry system can be variably configured for different requirements (cables, conductors, hoses, pneumatic and hydraulic lines).

Allmänna beställningsdata

Utförande	Inlägg, Cabtite (kabelinföringssystem), Polyamid, glasfiberförstärkt, Djupsvart, Höjd: 44 mm, Bredd: 44 mm, Djup: 17.5 mm, -40 °C...120 °C, IP66
Art.nr.	2584290000
Typ	CABTITE GI X BK
GTIN (EAN)	4050118616439
Förp.	5 items

Tekniska data

Godkännanden

Godkännanden



ROHS	Uppfyllelse
UL File Number Search	UL-webbplats
Certifikat nr (cURus)	E223801

Mått och vikter

Djup	17.5 mm	Byggdjup (tum)	0.689 inch
Höjd	44 mm	Bygghöjd (tum)	1.7323 inch
Höjd lägstbyggande	17.5 mm	Bredd	44 mm
Byggbredd (tum)	1.7323 inch	Nettovikt	5.04 g

Temperaturer

Drifttemperatur	-40 °C...120 °C
-----------------	-----------------

Miljööverensstämmelse för produkt

RoHS-kompatibilitetsstatus	Kompatibel utan undantag
REACH SVHC	Nej mSvHC över 0,1 viktprocent

Allmän information

Silikon	Nej	Brännbarhetsklass enligt UL 94	V-0
Halogener	Nej	Skyddsklass	IP66
Grundläggande material	Polyamid, glasfiberförstärkt	Tätning	TPE

Klassificeringar

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		

Profilritning

