

**CABTITE OFRL BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The frame, fabricated from a single piece, is quick and easy to assemble and consists of dimensionally stable, fibre-glass reinforced plastic. The captive foamed seal guarantees effective IP66 sealing in accordance with DIN EN 60529, even on painted and rough surfaces.

**Allmänna beställningsdata**

Utförande	Låsram, Cabtite (kabelinföringssystem), Polyamid, Djupsvart, Höjd: 77 mm, Bredd: 9 mm, Djup: 62 mm, -40 °C...120 °C
Art.nr.	<a href="#">2907560000</a>
Typ	CABTITE OFRL BK
GTIN (EAN)	4099986539549
Förp.	20 items

## CABTITE OFRL BK

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

## Tekniska data

## Godkännanden

Godkännanden



ROHS	Uppfyllelse
UL File Number Search	<a href="#">UL-webbplats</a>
Certifikat nr (cURus)	E223801

## Mått och vikter

Djup	62 mm	Byggdjup (tum)	2.4409 inch
Höjd	77 mm	Bygghöjd (tum)	3.0315 inch
Bredd	9 mm	Byggbredd (tum)	0.3543 inch
Nettovikt	2.7 g		

## Temperaturer

Drifttemperatur	-40 °C...120 °C
-----------------	-----------------

## Miljööverensstämmelse för produkt

RoHS-kompatibilitetsstatus	Kompatibel utan undantag
REACH SVHC	Nej mSvHC över 0,1 viktprocent

## Allmän information

Åtdragningsmoment	3 Nm	Silikon	Nej
Brännbarhetsklass enligt UL 94	V-0	Halogener	halogenfri
Grundläggande material	Polyamid		

## Klassificeringar

ETIM 8.0	EC002624	ETIM 9.0	EC002624
ETIM 10.0	EC002624	ECLASS 14.0	27-18-28-15
ECLASS 15.0	27-18-28-15		

**CABTITE OFRL BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

**Ritningar**

[www.weidmueller.com](http://www.weidmueller.com)

