

EW 35/SCHA/M3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

General ordering data

Version	End bracket, beige, TS 35, V-2, Wemid, Width: 16.5 mm, 100 °C
Order No.	0258660000
Type	EW 35/SCHA/M3
GTIN (EAN)	4008190033477
Qty.	20 items
Delivery status	This article will no longer be available in the future.
Last order date	2026-06-30T00:00:00+02:00
Alternative product	ZEW 35

EW 35/SCHA/M3

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	32.5 mm	Depth (inches)	1.2795 inch
Height	46 mm	Height (inches)	1.811 inch
Width	16.5 mm	Width (inches)	0.6496 inch
Net weight	9.78 g		

Temperatures

Ambient temperature	-50 °C...55 °C	Continuous operating temp., min.	-50 °C
Continuous operating temp., max.	100 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption	
RoHS Exemption (if applicable/known)	6c	
REACH SVHC	Lead 7439-92-1	
SCIP	ffc2e92d-f68c-4edd-8818-3ff53f901c61	
Product Carbon Footprint	Cradle to gate	0.111 kg CO2 eq.

Material data

Basic material	Wemid	Colour	beige
UL 94 flammability rating	V-2		

System specifications

Version	For the terminals	Mounting rail	TS 35
---------	-------------------	---------------	-------

Additional technical data

Installation advice	Direct mounting	Type of mounting	when screwed in
Locking	for screw fixing		

Dimensions

TS 35 offset	22.5 mm
--------------	---------

General

Installation advice	Direct mounting	Mounting rail	TS 35
---------------------	-----------------	---------------	-------

Classifications

ETIM 8.0	EC001041	ETIM 9.0	EC001041
ETIM 10.0	EC001041	ECLASS 14.0	27-25-03-02
ECLASS 15.0	27-25-03-02		