

SKMU M50 MS SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	SKMU MS (brass locknut), Locknut, M 50, 5 mm, Brass
Order No.	0930640006
Type	SKMU M50 MS SC
GTIN (EAN)	4032248976102
Qty.	5 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00
Alternative product	SKMU M50 MS

SKMU M50 MS SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	5 mm	Height (inches)	0.1968 inch
Net weight	67.2 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	f350dea6-3de1-42c5-a935-c4eb3e9d5e3c

General information

Pitch of thread	1.5 mm	Halogen	No
AF size 1	65 mm	Thickness	5.00 mm
Cable gland	M 50	Basic material	Brass
External thread	M 50	Internal thread	M 50
Length of thread	5 mm		

Classifications

ETIM 8.0	EC000940	ETIM 9.0	EC000940
ETIM 10.0	EC000940	ECLASS 14.0	27-14-08-05
ECLASS 15.0	27-14-08-05		

Drawings

