

KSP L24 S**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSP (Klippon shroud), Protective cap, 0 mm, Silicone
Order No.	0930700001
Type	KSP L24 S
GTIN (EAN)	4032248975969
Qty.	10 items
Delivery status	Discontinued
Available until	2023-07-30T00:00:00+02:00

KSP L24 S

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Height	80 mm	Height (inches)	3.1496 inch
Length	123 mm	Length (inches)	4.8425 inch
Net weight	21.6 g		

Temperatures

Operating temperature	-60 °C...200 °C
-----------------------	-----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	Yes	O.D.	28 mm
Operating temperature range, max.	200 °C	Operating temperature range, min.	-60 °C
Halogen	halogen-free	Thickness	1.50 mm
Basic material	Silicone	Internal thread	without
Length of thread	0 mm	Inside diameter D2	25.00 mm
Gap, internal dimension B	70.00 mm	Hardness (IRHD)	65

Classifications

ETIM 8.0	EC000441	ETIM 9.0	EC000441
ETIM 10.0	EC000441	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

Drawings

