

EA-RING MS/M40 SC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	EA (earthing rings), Earthing ring, Miscellaneous, M 40, Brass
Order No.	0930710005
Type	EA-RING MS/M40 SC
GTIN (EAN)	4032248976201
Qty.	10 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00
Alternative product	EA-RING MS/M 40

EA-RING MS/M40 SC

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	86.7 mm	Height (inches)	3.4134 inch
Length	86.7 mm	Length (inches)	3.4134 inch
Net weight	19.5 g		

Temperatures

Operating temperature

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	2bd73422-c6ea-4a92-b8e7-00964d1156f3

General information

O.D.	53 mm	Thickness	1.50 mm
Cable gland	M 40	Basic material	Brass
External thread	M 40	Inside diameter D2	13.50 mm
Gap, internal dimension B	45.40 mm	Width, outer dimension C	31.70 mm

Classifications

ETIM 8.0	EC002317	ETIM 9.0	EC002317
ETIM 10.0	EC002317	ECLASS 14.0	27-14-08-07
ECLASS 15.0	27-14-08-07		

EA-RING MS/M40 SC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

