

KSWF M16**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

In addition to cable glands for a wide range of applications, the product portfolio is rounded off by plugs, pressure compensation elements, adaptors and the corresponding accessories such as locknuts, sealing rings, flat washers and earthing rings.

General ordering data

Version	KSWF (flat gasket - vulcanised fibre), Sealing ring, M 16, Vulcanized fibre
Order No.	1076680000
Type	KSWF M16
GTIN (EAN)	4032248838615
Qty.	25 items
Delivery status	Discontinued
Available until	2024-08-31T00:00:00+02:00
Alternative product	KSWN M16

KSWF M16

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Height	1.5 mm	Height (inches)	0.0591 inch
Net weight	0.08 g		

Temperatures

Operating temperature	-40 °C...95 °C
-----------------------	----------------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

General information

Silicone	No	Number of wires	1
Operating temperature range, max.	95 °C	Operating temperature range, min.	-40 °C
Pitch of thread	1.5 mm	Cable gland	M 16
Basic material	Vulcanized fibre	Diameter of sealing ring	25.00 mm
External thread	M 16	Internal thread	M 16

Classifications

ETIM 8.0	EC001181	ETIM 9.0	EC001181
ETIM 10.0	EC001181	ECLASS 14.0	27-43-03-19
ECLASS 15.0	27-43-03-19		

Drawings

