


**WMF 2.5 FU BLZ PE 30-70V SW****Weidmüller Interface GmbH & Co. KG**Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**

In process control systems for facilities in the process and power generation sectors, incoming signals from field devices are often connected with terminal blocks in marshalling cabinets. Terminal blocks are used despite the existence of alternative technologies such as Remote I/O and Fieldbus. This is mainly because they offer a sturdy and simple connection system, and because they are clearly arranged. Our WMF (Weidmüller Multi Funktional) line of terminal blocks provide a multi-functional solution for marshalling signals.

**General ordering data**

|                 |                                                                                                                                 |
|-----------------|---------------------------------------------------------------------------------------------------------------------------------|
| Version         | Fuse terminal, Screw connection, black, 2.5 mm <sup>2</sup> , 6.3 A, 70 V, Number of connections: 4, Number of levels: 3, TS 35 |
| Order No.       | <a href="#">1162840000</a>                                                                                                      |
| Type            | WMF 2.5 FU BLZ PE 30-70V SW                                                                                                     |
| GTIN (EAN)      | 4032248992157                                                                                                                   |
| Qty.            | 50 items                                                                                                                        |
| Delivery status | Discontinued                                                                                                                    |
| Last order date | 2020-09-30T00:00:00+02:00                                                                                                       |

## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate No. (cURus) E60693

## Dimensions and weights

|                          |             |                |             |
|--------------------------|-------------|----------------|-------------|
| Depth                    | 74 mm       | Depth (inches) | 2.9134 inch |
| Depth including DIN rail | 74.5 mm     | Height         | 90 mm       |
| Height (inches)          | 3.5433 inch | Width          | 5.08 mm     |
| Width (inches)           | 0.2 inch    | Net weight     | 21.66 g     |

## Temperatures

|                                  |                |                                  |               |
|----------------------------------|----------------|----------------------------------|---------------|
| Storage temperature              | -25 °C...55 °C | Ambient temperature              | -5 °C...40 °C |
| Continuous operating temp., min. | -50 °C         | Continuous operating temp., max. | 120 °C        |

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Material data

|                           |       |        |       |
|---------------------------|-------|--------|-------|
| Basic material            | Wemid | Colour | black |
| UL 94 flammability rating | V-0   |        |       |

## System specifications

|                  |                                                                                                                                                      |                          |       |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|-------|
| Version          | 2 screw connections -<br>1 plug-in connection,<br>Fuse isolator, With PE<br>connection, for plug-in<br>cross-connector, One end<br>without connector | End cover plate required | Yes   |
| Number of levels | 3                                                                                                                                                    | Mounting rail            | TS 35 |

## Additional technical data

|            |       |                  |         |
|------------|-------|------------------|---------|
| Open sides | right | Type of mounting | Snap-on |
|------------|-------|------------------|---------|

## CSA rating data

|                               |        |                       |                |
|-------------------------------|--------|-----------------------|----------------|
| Wire cross section max. (CSA) | 12 AWG | Certificate No. (CSA) | 200039-1057876 |
| Voltage size B (CSA)          | 300 V  | Current size B (CSA)  | 17 A           |
| Voltage size D (CSA)          | 300 V  | Current size D (CSA)  | 10 A           |
| Wire cross section min. (CSA) | 26 AWG |                       |                |

## Conductors for clamping (additional connection)

|                                            |         |                                        |                    |
|--------------------------------------------|---------|----------------------------------------|--------------------|
| Connection direction additional connection | on side | Connection type, additional connection | Plug-in connection |
|--------------------------------------------|---------|----------------------------------------|--------------------|

## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Conductors for clamping (rated connection)

|                                                                                         |                     |                                                                                         |                     |
|-----------------------------------------------------------------------------------------|---------------------|-----------------------------------------------------------------------------------------|---------------------|
| Gauge to IEC 60947-1                                                                    | A3                  | Wire connection cross section AWG, max.                                                 | AWG 12              |
| Connection direction                                                                    | on side             | Tightening torque, max.                                                                 | 0.6 Nm              |
| Tightening torque, min.                                                                 | 0.5 Nm              | Stripping length                                                                        | 10 mm               |
| Type of connection 2                                                                    | Plug-in connection  | Type of connection                                                                      | Screw connection    |
| Number of connections                                                                   | 4                   | Clamping range, max.                                                                    | 4 mm <sup>2</sup>   |
| Clamping range, min.                                                                    | 0.5 mm <sup>2</sup> | Clamping screw                                                                          | M 3                 |
| Blade size                                                                              | 0.6 x 3.5 mm        | Wire connection cross section AWG, min.                                                 | AWG 26              |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max. | 2.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max. | 2.5 mm <sup>2</sup> | Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min. | 0.5 mm <sup>2</sup> |
| Wire connection cross section, finely stranded, max.                                    | 4 mm <sup>2</sup>   | Wire connection cross section, finely stranded, min.                                    | 0.5 mm <sup>2</sup> |
| Connection cross-section, stranded, max.                                                | 4 mm <sup>2</sup>   | Connection cross-section, stranded, min. 1.5 mm <sup>2</sup>                            |                     |
| Wire connection cross-section, solid core, max.                                         | 4 mm <sup>2</sup>   | Wire connection cross-section, solid core, min.                                         | 0.5 mm <sup>2</sup> |

## General

|                                         |                                                                           |                                         |        |
|-----------------------------------------|---------------------------------------------------------------------------|-----------------------------------------|--------|
| Wire connection cross section AWG, max. | AWG 12                                                                    | Wire connection cross section AWG, min. | AWG 26 |
| Standards                               | IEC 60947-7-2, IEC 61984, In accordance with IEC 60947-7-1, IEC 60947-7-3 | Mounting rail                           | TS 35  |

## Rating data

|                                              |                     |                                 |                                                                           |
|----------------------------------------------|---------------------|---------------------------------|---------------------------------------------------------------------------|
| Rated cross-section                          | 2.5 mm <sup>2</sup> | Rated voltage                   | 70 V                                                                      |
| Rated DC voltage                             | 70 V                | Nominal current                 | 6.3 A                                                                     |
| Current at maximum wires                     | 6.3 A               | Standards                       | IEC 60947-7-2, IEC 61984, In accordance with IEC 60947-7-1, IEC 60947-7-3 |
| Volume resistance according to IEC 60947-7-x | 1.33 mΩ             | Rated impulse withstand voltage | 8 kV                                                                      |
| Power loss in accordance with IEC 60947-7-x  | 0.77 W              | Surge voltage category          | III                                                                       |
| Pollution severity                           | 3                   |                                 |                                                                           |

## UL rating data

|                                            |        |                                            |        |
|--------------------------------------------|--------|--------------------------------------------|--------|
| Conductor size Factory wiring max. (cURus) | 12 AWG | Voltage size B (cURus)                     | 300 V  |
| Voltage size D (cURus)                     | 300 V  | Wire cross section max. (cURus)            | 12 AWG |
| Certificate No. (cURus)                    | E60693 | Wire cross section min. (cURus)            | 26 AWG |
| Conductor size Field wiring min. (cURus)   | 26 AWG | Conductor size Factory wiring min. (cURus) | 26 AWG |
| Current size B (cURus)                     | 17 A   | Current size D (cURus)                     | 10 A   |
| Conductor size Field wiring max. (cURus)   | 12 AWG |                                            |        |

## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)


## Technical data

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000899    | ETIM 9.0    | EC000899    |
| ETIM 10.0   | EC000899    | ECLASS 14.0 | 27-25-01-13 |
| ECLASS 15.0 | 27-25-01-13 |             |             |

### WMF 2.5 FU BLZ PE 30-70V SW

## Drawings



## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

## Accessories




The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

## General ordering data

|            |                            |                                                                  |
|------------|----------------------------|------------------------------------------------------------------|
| Type       | AP WMF2.5                  | Version                                                          |
| Order No.  | <a href="#">1142990000</a> | End plate for terminals, beige, Height: 87.25 mm, Width: 1.5 mm, |
| GTIN (EAN) | 4032248925889              | V-0, Wemid, Snap-on: Yes                                         |
| Qty.       | 50 ST                      |                                                                  |

## End bracket



Weidmüller's range of products includes end brackets that guarantee a permanent, reliable mounting on the terminal rail and prevent sliding. Versions with and without screws are available. The end brackets include marking options, also for group markers, and also a test plug holder.

## General ordering data

|            |                            |                                                                |
|------------|----------------------------|----------------------------------------------------------------|
| Type       | WEW 35/2                   | Version                                                        |
| Order No.  | <a href="#">1061200000</a> | End bracket, dark beige, TS 35, HB, Wemid, Width: 8 mm, 100 °C |
| GTIN (EAN) | 4008190030230              |                                                                |
| Qty.       | 50 ST                      |                                                                |

## Accessories



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

## General ordering data

|            |                            |                                                                                     |
|------------|----------------------------|-------------------------------------------------------------------------------------|
| Type       | WBB WMF2.5 BLZ             | Version                                                                             |
| Order No.  | <a href="#">1142980000</a> | Partition plate (terminal), dark beige, Height: 88.5 mm, Width: 5.08 mm, V-0, Wemid |
| GTIN (EAN) | 4032248925896              |                                                                                     |
| Qty.       | 10 ST                      |                                                                                     |

## WMF 2.5 FU BLZ PE 30-70V SW

Weidmüller Interface GmbH &amp; Co. KG


Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Accessories

|            |                            |                                         |
|------------|----------------------------|-----------------------------------------|
| Type       | IL WMF2.5 BLZ OR           | Version                                 |
| Order No.  | <a href="#">1167440000</a> | Locking clips (terminal), PA 66, orange |
| GTIN (EAN) | 4032248958474              |                                         |
| Qty.       | 50 ST                      |                                         |

## Slotted screwdriver




Slotted screwdriver with rounded blade SD DIN 5265, ISO 2380/2, output to DIN 5264, ISO 2380/1. ChromTop tip, SoftFinish grip

## General ordering data

|            |                            |                          |
|------------|----------------------------|--------------------------|
| Type       | SDS 0.6X3.5X100            | Version                  |
| Order No.  | <a href="#">9008330000</a> | Screwdriver, Screwdriver |
| GTIN (EAN) | 4032248056286              |                          |
| Qty.       | 1 ST                       |                          |

## BLZP 5.08HC/90 SN



Female plugs with clamping-yoke connection for connecting wires with a right-angle (90° or 270°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. They also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

## General ordering data

|            |                            |                                                                                                                                   |
|------------|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------|
| Type       | BLZP 5.08HC/02/90 SN BK... | Version                                                                                                                           |
| Order No.  | <a href="#">1948240000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 2, 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| GTIN (EAN) | 4032248624768              |                                                                                                                                   |
| Qty.       | 180 ST                     |                                                                                                                                   |
| Type       | BLZP 5.08HC/02/90 SN OR... | Version                                                                                                                           |
| Order No.  | <a href="#">1948000000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 2, 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| GTIN (EAN) | 4032248624225              |                                                                                                                                   |
| Qty.       | 180 ST                     |                                                                                                                                   |
| Type       | BLZP 5.08HC/03/90 SN BK... | Version                                                                                                                           |
| Order No.  | <a href="#">1948250000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 3, 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| GTIN (EAN) | 4032248624775              |                                                                                                                                   |
| Qty.       | 120 ST                     |                                                                                                                                   |
| Type       | BLZP 5.08HC/03/90 SN OR... | Version                                                                                                                           |
| Order No.  | <a href="#">1948010000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 3, 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| GTIN (EAN) | 4032248624232              |                                                                                                                                   |
| Qty.       | 120 ST                     |                                                                                                                                   |

## WMF 2.5 FU BLZ PE 30-70V SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | BLZP 5.08HC/04/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948260000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 4,  |
| GTIN (EAN) | 4032248624782              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 90 ST                      |                                                                   |
| Type       | BLZP 5.08HC/04/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948020000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 4,  |
| GTIN (EAN) | 4032248624249              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 90 ST                      |                                                                   |
| Type       | BLZP 5.08HC/05/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948270000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 5,  |
| GTIN (EAN) | 4032248624799              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 72 ST                      |                                                                   |
| Type       | BLZP 5.08HC/05/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948030000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 5,  |
| GTIN (EAN) | 4032248624256              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 72 ST                      |                                                                   |
| Type       | BLZP 5.08HC/06/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948280000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 6,  |
| GTIN (EAN) | 4032248624805              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 60 ST                      |                                                                   |
| Type       | BLZP 5.08HC/06/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948040000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 6,  |
| GTIN (EAN) | 4032248624263              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 60 ST                      |                                                                   |
| Type       | BLZP 5.08HC/07/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948290000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 7,  |
| GTIN (EAN) | 4032248624812              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 48 ST                      |                                                                   |
| Type       | BLZP 5.08HC/07/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948050000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 7,  |
| GTIN (EAN) | 4032248624270              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 48 ST                      |                                                                   |
| Type       | BLZP 5.08HC/08/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948300000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 8,  |
| GTIN (EAN) | 4032248624829              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 42 ST                      |                                                                   |
| Type       | BLZP 5.08HC/08/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948060000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 8,  |
| GTIN (EAN) | 4032248624287              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 42 ST                      |                                                                   |
| Type       | BLZP 5.08HC/09/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948310000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 9,  |
| GTIN (EAN) | 4032248624836              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |
| Type       | BLZP 5.08HC/09/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948070000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 9,  |
| GTIN (EAN) | 4032248624294              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |
| Type       | BLZP 5.08HC/10/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948320000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 10, |
| GTIN (EAN) | 4032248624843              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |



## WMF 2.5 FU BLZ PE 30-70V SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | BLZP 5.08HC/10/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948080000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 10, |
| GTIN (EAN) | 4032248624300              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |
| Type       | BLZP 5.08HC/11/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948330000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 11, |
| GTIN (EAN) | 4032248624850              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/11/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948100000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 11, |
| GTIN (EAN) | 4032248624522              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/12/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948340000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 12, |
| GTIN (EAN) | 4032248624867              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/12/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948110000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 12, |
| GTIN (EAN) | 4032248624539              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/13/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948350000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 13, |
| GTIN (EAN) | 4032248624874              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/13/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948120000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 13, |
| GTIN (EAN) | 4032248624546              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/14/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948360000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 14, |
| GTIN (EAN) | 4032248624881              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/14/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948130000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 14, |
| GTIN (EAN) | 4032248624553              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/15/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948370000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 15, |
| GTIN (EAN) | 4032248624898              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/15/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948140000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 15, |
| GTIN (EAN) | 4032248624560              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/16/90 SN BK... | Version                                                           |
| Order No.  | <a href="#">1948380000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4032248624904              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/16/90 SN OR... | Version                                                           |
| Order No.  | <a href="#">1948150000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4032248624577              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |


## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## BLZP 5.08HC/90F SN



Female plugs with clamping-yoke connection for connecting wires with a right-angle (90° or 270°) outlet direction. The female connectors provide space for labelling and can be coded. Fastened by means of a flange or release latch. They also provide an integrated plus/minus screw, protection against faulty insertion of the wire, and they are delivered with open clamping yokes. HC = High Current.

## General ordering data

|            |                            |                                                                  |
|------------|----------------------------|------------------------------------------------------------------|
| Type       | BLZP 5.08HC/02/90F SN B... | Version                                                          |
| Order No.  | <a href="#">1950040000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 2, |
| GTIN (EAN) | 4032248627974              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 90 ST                      |                                                                  |
| Type       | BLZP 5.08HC/02/90F SN O... | Version                                                          |
| Order No.  | <a href="#">1949800000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 2, |
| GTIN (EAN) | 4032248627721              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 90 ST                      |                                                                  |
| Type       | BLZP 5.08HC/03/90F SN B... | Version                                                          |
| Order No.  | <a href="#">1950050000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 3, |
| GTIN (EAN) | 4032248627981              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 72 ST                      |                                                                  |
| Type       | BLZP 5.08HC/03/90F SN O... | Version                                                          |
| Order No.  | <a href="#">1949810000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 3, |
| GTIN (EAN) | 4032248627738              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 72 ST                      |                                                                  |
| Type       | BLZP 5.08HC/04/90F SN B... | Version                                                          |
| Order No.  | <a href="#">1950060000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 4, |
| GTIN (EAN) | 4032248627998              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 60 ST                      |                                                                  |
| Type       | BLZP 5.08HC/04/90F SN O... | Version                                                          |
| Order No.  | <a href="#">1949820000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 4, |
| GTIN (EAN) | 4032248627745              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 60 ST                      |                                                                  |
| Type       | BLZP 5.08HC/05/90F SN B... | Version                                                          |
| Order No.  | <a href="#">1950070000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 5, |
| GTIN (EAN) | 4032248628001              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 48 ST                      |                                                                  |
| Type       | BLZP 5.08HC/05/90F SN O... | Version                                                          |
| Order No.  | <a href="#">1949830000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 5, |
| GTIN (EAN) | 4032248627752              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 48 ST                      |                                                                  |
| Type       | BLZP 5.08HC/06/90F SN B... | Version                                                          |
| Order No.  | <a href="#">1950080000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 6, |
| GTIN (EAN) | 4032248628018              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 42 ST                      |                                                                  |
| Type       | BLZP 5.08HC/06/90F SN G... | Version                                                          |
| Order No.  | <a href="#">1284860000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 6, |
| GTIN (EAN) | 4050118075410              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box |
| Qty.       | 42 ST                      |                                                                  |

## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | BLZP 5.08HC/06/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949840000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 6,  |
| GTIN (EAN) | 4032248627769              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 42 ST                      |                                                                   |
| Type       | BLZP 5.08HC/07/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950090000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 7,  |
| GTIN (EAN) | 4032248628025              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |
| Type       | BLZP 5.08HC/07/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949850000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 7,  |
| GTIN (EAN) | 4032248627776              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |
| Type       | BLZP 5.08HC/08/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950100000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 8,  |
| GTIN (EAN) | 4032248628032              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |
| Type       | BLZP 5.08HC/08/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949860000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 8,  |
| GTIN (EAN) | 4032248627783              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 36 ST                      |                                                                   |
| Type       | BLZP 5.08HC/09/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950110000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 9,  |
| GTIN (EAN) | 4032248628049              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/09/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949870000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 9,  |
| GTIN (EAN) | 4032248627790              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/10/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950120000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 10, |
| GTIN (EAN) | 4032248628056              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/10/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949880000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 10, |
| GTIN (EAN) | 4032248627806              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 30 ST                      |                                                                   |
| Type       | BLZP 5.08HC/11/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950130000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 11, |
| GTIN (EAN) | 4032248628063              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/11/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949890000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 11, |
| GTIN (EAN) | 4032248627813              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/12/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950140000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 12, |
| GTIN (EAN) | 4032248628070              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/12/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949900000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 12, |
| GTIN (EAN) | 4032248627837              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |

## WMF 2.5 FU BLZ PE 30-70V SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | BLZP 5.08HC/13/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950150000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 13, |
| GTIN (EAN) | 4032248628087              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/13/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949910000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 13, |
| GTIN (EAN) | 4032248627844              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 24 ST                      |                                                                   |
| Type       | BLZP 5.08HC/14/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950160000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 14, |
| GTIN (EAN) | 4032248628094              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/14/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949920000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 14, |
| GTIN (EAN) | 4032248627851              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/15/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950170000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 15, |
| GTIN (EAN) | 4032248628100              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/15/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949930000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 15, |
| GTIN (EAN) | 4032248627868              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/16/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950180000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4032248628117              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/16/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949940000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 16, |
| GTIN (EAN) | 4032248627875              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/17/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950190000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 17, |
| GTIN (EAN) | 4032248628124              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/17/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949950000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 17, |
| GTIN (EAN) | 4032248627882              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/18/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950200000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 18, |
| GTIN (EAN) | 4032248628131              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/18/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949960000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 18, |
| GTIN (EAN) | 4032248627899              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 18 ST                      |                                                                   |
| Type       | BLZP 5.08HC/19/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950210000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 19, |
| GTIN (EAN) | 4032248628148              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |

## WMF 2.5 FU BLZ PE 30-70V SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | BLZP 5.08HC/19/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949970000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 19, |
| GTIN (EAN) | 4032248627905              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/20/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950220000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 20, |
| GTIN (EAN) | 4032248628155              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/20/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949980000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 20, |
| GTIN (EAN) | 4032248627912              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/21/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950230000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 21, |
| GTIN (EAN) | 4032248628162              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/21/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1949990000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 21, |
| GTIN (EAN) | 4032248627929              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/22/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950240000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 22, |
| GTIN (EAN) | 4032248628179              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/22/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1950010000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 22, |
| GTIN (EAN) | 4032248627936              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/23/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950250000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 23, |
| GTIN (EAN) | 4032248628186              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/23/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1950020000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 23, |
| GTIN (EAN) | 4032248627950              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/24/90F SN B... | Version                                                           |
| Order No.  | <a href="#">1950260000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 24, |
| GTIN (EAN) | 4032248628193              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |
| Type       | BLZP 5.08HC/24/90F SN O... | Version                                                           |
| Order No.  | <a href="#">1950030000</a> | PCB plug-in connector, female plug, 5.08 mm, Number of poles: 24, |
| GTIN (EAN) | 4032248627967              | 90°, Clamping yoke connection, Clamping range, max. : 4 mm², Box  |
| Qty.       | 12 ST                      |                                                                   |

## WMF 2.5 FU BLZ PE 30-70V SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

## Accessories



The comprehensive accessories of the Klippon® Connect portfolio are perfectly matched down to the last detail. This facilitates mounting while adhering to required norms

## General ordering data

|            |                            |                                                                   |
|------------|----------------------------|-------------------------------------------------------------------|
| Type       | WAD WMF2.5                 | Version                                                           |
| Order No.  | <a href="#">1142970000</a> | Terminal cover, dark beige, Wemid, Height: 11 mm, Width: 9.96 mm, |
| GTIN (EAN) | 4032248926039              | Depth: 9.68 mm, V-0                                               |
| Qty.       | 50 ST                      |                                                                   |

## Blank



The Dekafix (DEK) marker is the universal marker for all conductor and plug-in connectors as well as for electronic sub-assemblies. The system is ideal for short number sequences and covers a wide range of ready-printed markers.

Strips for fast installation in only one work step. The printing is easy to read, rich in contrast and available in various widths.

- Large range of ready-to-use markers
  - Strips for fast installation
  - Terminal markers, suitable for all Weidmüller cable connectors
  - Available as blank MultiCard or with standard printing
- For custom printing: Please send us a file of our labeling software M-Print PRO or M-Print PRO Online (without installation) for your labeling specifications.

## General ordering data

|            |                            |                                                                    |
|------------|----------------------------|--------------------------------------------------------------------|
| Type       | DEK 5/5 MC NE WS           | Version                                                            |
| Order No.  | <a href="#">1609801044</a> | Dekafix, Terminal marker, 5 x 5 mm, Pitch in mm (P): 5.00          |
| GTIN (EAN) | 4008190397111              | Weidmueller, white                                                 |
| Qty.       | 1000 ST                    |                                                                    |
| Type       | WS 10/5 M MC NE WS         | Version                                                            |
| Order No.  | <a href="#">1792000000</a> | WS, Terminal marker, 10 x 5 mm, Pitch in mm (P): 5.00 Weidmueller, |
| GTIN (EAN) | 4032248223862              | Allen-Bradley, white                                               |
| Qty.       | 720 ST                     |                                                                    |


## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

## Marker holder



The marker holder offer the possibility of additional mounting of standard markers with a pitch of 5 or 5.1 mm. The angled holders can be optionally snapped together and could be mounted in all standard marking channels of the Klippon® Connect modular terminal blocks. Fitting marker types could be found under the respective accessories of the designation marking holder.

## General ordering data

|            |                            |                            |
|------------|----------------------------|----------------------------|
| Type       | BZT 1 WS 10/5              | Version                    |
| Order No.  | <a href="#">1805490000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270231              |                            |
| Qty.       | 100 ST                     |                            |
| Type       | BZT 1 ZA WS 10/5           | Version                    |
| Order No.  | <a href="#">1805520000</a> | Accessories, Marker holder |
| GTIN (EAN) | 4032248270248              |                            |
| Qty.       | 100 ST                     |                            |

## Cross-connections



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

## General ordering data

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | ZQV 2.5N/10                | Version                                                               |
| Order No.  | <a href="#">1527690000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447989              | 10, Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm             |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/10 BL             | Version                                                               |
| Order No.  | <a href="#">1527880000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 10, |
| GTIN (EAN) | 4050118448573              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/10 RD             | Version                                                               |
| Order No.  | <a href="#">2108910000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 10,  |
| GTIN (EAN) | 4050118486018              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 48.7 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/2                 | Version                                                               |
| Order No.  | <a href="#">1527540000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448467              | 2, Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm               |
| Qty.       | 60 ST                      |                                                                       |

## WMF 2.5 FU BLZ PE 30-70V SW

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | ZQV 2.5N/2 BL              | Version                                                               |
| Order No.  | <a href="#">1527740000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 2,  |
| GTIN (EAN) | 4050118448658              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/2 RD              | Version                                                               |
| Order No.  | <a href="#">2108470000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 2,   |
| GTIN (EAN) | 4050118448542              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 7.9 mm                  |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/20                | Version                                                               |
| Order No.  | <a href="#">1527720000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118447972              | 20, Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/20 BL             | Version                                                               |
| Order No.  | <a href="#">1527890000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 20, |
| GTIN (EAN) | 4050118448566              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/20 RD             | Version                                                               |
| Order No.  | <a href="#">2108920000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 20,  |
| GTIN (EAN) | 4050118485899              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 102 mm                  |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/3                 | Version                                                               |
| Order No.  | <a href="#">1527570000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448450              | 3, Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/3 BL              | Version                                                               |
| Order No.  | <a href="#">1527770000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 3,  |
| GTIN (EAN) | 4050118448641              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                   |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/3 RD              | Version                                                               |
| Order No.  | <a href="#">2108690000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 3,   |
| GTIN (EAN) | 4050118448535              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 13 mm                   |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/4                 | Version                                                               |
| Order No.  | <a href="#">1527590000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448443              | 4, Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm              |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/4 BL              | Version                                                               |
| Order No.  | <a href="#">1527780000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 4,  |
| GTIN (EAN) | 4050118448634              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                 |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/4 RD              | Version                                                               |
| Order No.  | <a href="#">2108700000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 4,   |
| GTIN (EAN) | 4050118448528              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 18.1 mm                 |
| Qty.       | 60 ST                      |                                                                       |
| Type       | ZQV 2.5N/5                 | Version                                                               |
| Order No.  | <a href="#">1527620000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448436              | 5, Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/5 BL              | Version                                                               |
| Order No.  | <a href="#">1527790000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 5,  |
| GTIN (EAN) | 4050118448627              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                 |
| Qty.       | 20 ST                      |                                                                       |



## WMF 2.5 FU BLZ PE 30-70V SW

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Accessories

|            |                            |                                                                       |
|------------|----------------------------|-----------------------------------------------------------------------|
| Type       | ZQV 2.5N/5 RD              | Version                                                               |
| Order No.  | <a href="#">2108710000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 5,   |
| GTIN (EAN) | 4050118448511              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 23.2 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/50                | Version                                                               |
| Order No.  | <a href="#">1527730000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118411362              | 50, Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm              |
| Qty.       | 5 ST                       |                                                                       |
| Type       | ZQV 2.5N/50 BL             | Version                                                               |
| Order No.  | <a href="#">1527920000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 50, |
| GTIN (EAN) | 4050118448559              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 ST                       |                                                                       |
| Type       | ZQV 2.5N/50 RD             | Version                                                               |
| Order No.  | <a href="#">2109000000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 50,  |
| GTIN (EAN) | 4050118486001              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 255 mm                  |
| Qty.       | 5 ST                       |                                                                       |
| Type       | ZQV 2.5N/6                 | Version                                                               |
| Order No.  | <a href="#">1527630000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448429              | 6, Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/6 BL              | Version                                                               |
| Order No.  | <a href="#">1527820000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 6,  |
| GTIN (EAN) | 4050118448610              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/6 RD              | Version                                                               |
| Order No.  | <a href="#">2108720000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 6,   |
| GTIN (EAN) | 4050118448504              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 28.3 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/7                 | Version                                                               |
| Order No.  | <a href="#">1527640000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448412              | 7, Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/7 BL              | Version                                                               |
| Order No.  | <a href="#">1527830000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 7,  |
| GTIN (EAN) | 4050118448603              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/7 RD              | Version                                                               |
| Order No.  | <a href="#">2108810000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 7,   |
| GTIN (EAN) | 4050118448498              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 33.4 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/8                 | Version                                                               |
| Order No.  | <a href="#">1527670000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:   |
| GTIN (EAN) | 4050118448405              | 8, Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm              |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/8 BL              | Version                                                               |
| Order No.  | <a href="#">1527840000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 8,  |
| GTIN (EAN) | 4050118448597              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 ST                      |                                                                       |
| Type       | ZQV 2.5N/8 RD              | Version                                                               |
| Order No.  | <a href="#">2108870000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 8,   |
| GTIN (EAN) | 4050118448481              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 38.5 mm                 |
| Qty.       | 20 ST                      |                                                                       |

**WMF 2.5 FU BLZ PE 30-70V SW****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Accessories**

|            |                            |                                                                      |
|------------|----------------------------|----------------------------------------------------------------------|
| Type       | ZQV 2.5N/9                 | Version                                                              |
| Order No.  | <a href="#">1527680000</a> | Cross-connector (terminal), Plugged, orange, 24 A, Number of poles:  |
| GTIN (EAN) | 4050118447996              | 9, Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm             |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/9 BL              | Version                                                              |
| Order No.  | <a href="#">1527870000</a> | Cross-connector (terminal), Plugged, blue, 24 A, Number of poles: 9, |
| GTIN (EAN) | 4050118448580              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                |
| Qty.       | 20 ST                      |                                                                      |
| Type       | ZQV 2.5N/9 RD              | Version                                                              |
| Order No.  | <a href="#">2108900000</a> | Cross-connector (terminal), Plugged, red, 24 A, Number of poles: 9,  |
| GTIN (EAN) | 4050118448474              | Pitch in mm (P): 5.10, Insulated: Yes, Width: 43.6 mm                |
| Qty.       | 20 ST                      |                                                                      |