


ES EPG 45 HEX 10/70**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Version	70mm ² , Hexagonal crimp
Order No.	1500940000
Type	ES EPG 45 HEX 10/70
GTIN (EAN)	4050118309522
Qty.	1 items

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	12 mm	Depth (inches)	0.4724 inch
Height	60 mm	Height (inches)	2.3622 inch
Width	30 mm	Width (inches)	1.1811 inch
Net weight	130 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Crimp inserts

Identification number	6/16	Crimp cross-section aluminium	-/50
Crimp cross-section copper	10/70	Crimping width in mm	7/5

Description of contact

Conductor cross-section, max. AWG	2/0	Conductor cross-section, min. AWG	8
Crimping range, max.	70 mm ²		

tool data crimping

Crimping type/profile	Hexagonal crimp		
Cable lug cross section	nominal	10 mm ²	
	nominal	70 mm ²	

Classifications

ETIM 8.0	EC001282	ETIM 9.0	EC001282
ETIM 10.0	EC001282	ECLASS 14.0	21-04-90-90
ECLASS 15.0	21-04-90-90		

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

Tools



Crimping tools for cable lugs, connectors and wire-end ferrules with interchangeable inserts

- extremely fast processing thanks to hydraulic support
- large processing range up to 300 mm²
- 270° revolving quick-action crimping head
- automatic pressure limitation and monitoring via pressure sensor
- electronic control and monitoring of the crimping process
- Saving of all crimping cycles and error messages to internal memory
- Reading of all cycles and error messages via USB
- Li-ion rechargeable battery with charge status indicator: 18 V, 2 Ah

General ordering data

Type	EPG 45	Version
Order No.	1500830000	Pressing tool, 6mm ² , 150mm ² , Hexagonal crimp, WM crimp, Indent
GTIN (EAN)	4050118309317	crimp, Trapezoidal crimp, Oval crimping
Qty.	1 ST	

10 mm²10 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M4/-10	Version
Order No.	1496900000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306293	
Qty.	100 ST	
Type	KRN-M5/-10	Version
Order No.	1496910000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306378	
Qty.	100 ST	
Type	KRN-M6/-10	Version
Order No.	1496920000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306439	
Qty.	100 ST	
Type	KRN-M8/-10	Version
Order No.	1496930000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306552	
Qty.	100 ST	

ES EPG 45 HEX 10/70


Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KRN-M10/-10	Version
Order No.	1496940000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306521	
Qty.	100 ST	
Type	KRN-M12/-10	Version
Order No.	1496950000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306453	
Qty.	100 ST	

70 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KRN-M6/-70	Version
Order No.	1496640000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305951	
Qty.	25 ST	
Type	KRN-M8/-70	Version
Order No.	1496650000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305791	
Qty.	25 ST	
Type	KRN-M10/-70	Version
Order No.	1496670000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305845	
Qty.	25 ST	
Type	KRN-M12/-70	Version
Order No.	1495570000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118304992	
Qty.	25 ST	
Type	KRN-M14/-70	Version
Order No.	1495770000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305166	
Qty.	25 ST	
Type	KRN-M16/-70	Version
Order No.	1495800000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305340	
Qty.	25 ST	
Type	KRN-M20/-70	Version
Order No.	1495590000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305302	
Qty.	25 ST	

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KRN-M6/-70 S	Version
Order No.	1494850000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304152	
Qty.	25 ST	
Type	KRN-M8/-70 S	Version
Order No.	1494860000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304527	
Qty.	25 ST	
Type	KRN-M10/-70 S	Version
Order No.	1494870000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304503	
Qty.	25 ST	
Type	KRN-M12/-70 S	Version
Order No.	1494880000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304435	
Qty.	25 ST	

10 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWN-M5/-10 90	Version
Order No.	1497020000	cable lug, terminal end,10 mm ² ,10 mm ² - 10 mm ²
GTIN (EAN)	4050118306712	
Qty.	100 ST	
Type	KWN-M6/-10 90	Version
Order No.	1497030000	cable lug, terminal end,10 mm ² ,10 mm ² - 10 mm ²
GTIN (EAN)	4050118306484	
Qty.	100 ST	
Type	KWN-M8/-10 90	Version
Order No.	1497040000	cable lug, terminal end,10 mm ² ,10 mm ² - 10 mm ²
GTIN (EAN)	4050118306576	
Qty.	100 ST	
Type	KWN-M10/-10 90	Version
Order No.	1497050000	cable lug, terminal end,10 mm ² ,10 mm ² - 10 mm ²
GTIN (EAN)	4050118306750	
Qty.	100 ST	
Type	KWN-M12/-10 90	Version
Order No.	1497070000	cable lug, terminal end,10 mm ² ,10 mm ² - 10 mm ²
GTIN (EAN)	4050118306606	
Qty.	100 ST	

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

70 mm²70 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWN-M6/-70 90	Version
Order No.	1496010000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305609	
Qty.	25 ST	
Type	KWN-M8/-70 90	Version
Order No.	1496020000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305180	
Qty.	25 ST	
Type	KWN-M10/-70 90	Version
Order No.	1496030000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305432	
Qty.	25 ST	
Type	KWN-M12/-70 90	Version
Order No.	1496040000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305463	
Qty.	25 ST	
Type	KWN-M14/-70 90	Version
Order No.	1494660000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118304183	
Qty.	25 ST	
Type	KWN-M16/-70 90	Version
Order No.	1496050000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305708	
Qty.	25 ST	
Type	KWN-M20/-70 90	Version
Order No.	1496070000	cable lug, terminal end,70 mm ² ,70 mm ² - 70 mm ²
GTIN (EAN)	4050118305661	
Qty.	25 ST	

10 mm²10 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

General ordering data

Type	KWN-M5/-10 45	Version
Order No.	1496810000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306309	
Qty.	100 ST	
Type	KWN-M6/-10 45	Version
Order No.	1496820000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306286	
Qty.	100 ST	
Type	KWN-M8/-10 45	Version
Order No.	1496830000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306330	
Qty.	100 ST	
Type	KWN-M10/-10 45	Version
Order No.	1496840000	cable lug, terminal end, 10 mm ² , 10 mm ² - 10 mm ²
GTIN (EAN)	4050118306361	
Qty.	100 ST	

70 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWN-M8/-70 45	Version
Order No.	1496310000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305944	
Qty.	25 ST	
Type	KWN-M10/-70 45	Version
Order No.	1496320000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118306255	
Qty.	25 ST	
Type	KWN-M12/-70 45	Version
Order No.	1496330000	cable lug, terminal end, 70 mm ² , 70 mm ² - 70 mm ²
GTIN (EAN)	4050118305586	
Qty.	25 ST	

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

10 mm²

10 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VSTN/-10	Version
Order No.	1497130000	cable lug, terminal end, 10 mm ² , 10 mm ² , None
GTIN (EAN)	4050118306491	
Qty.	50 ST	
Type	KP-M5/-10	Version
Order No.	1497870000	cable lug, terminal end, 10 mm ²
GTIN (EAN)	4050118307252	
Qty.	100 ST	
Type	KP-M6/-10	Version
Order No.	1497880000	cable lug, terminal end, 10 mm ²
GTIN (EAN)	4050118307283	
Qty.	100 ST	
Type	KP-M8/-10	Version
Order No.	1497890000	cable lug, terminal end, 10 mm ²
GTIN (EAN)	4050118307573	
Qty.	100 ST	
Type	KP-M10/-10	Version
Order No.	1497910000	cable lug, terminal end, 10 mm ²
GTIN (EAN)	4050118307276	
Qty.	100 ST	

70 mm²

70 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KP-M8/-70	Version
Order No.	1498130000	cable lug, terminal end, 70 mm ²
GTIN (EAN)	4050118307351	
Qty.	50 ST	

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KP-M10/-70	Version
Order No.	1498140000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307429	
Qty.	50 ST	
Type	KP-M12/-70	Version
Order No.	1498150000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307467	
Qty.	50 ST	
Type	KP-M14/-70	Version
Order No.	1498560000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307696	
Qty.	50 ST	
Type	KP-M16/-70	Version
Order No.	1498160000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307481	
Qty.	50 ST	
Type	KP-M20/-70	Version
Order No.	1498170000	cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307344	
Qty.	50 ST	

10 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWPN-M6/-10 90	Version
Order No.	1497420000	cable lug, terminal end,10 mm ²
GTIN (EAN)	4050118307023	
Qty.	100 ST	
Type	KWPN-M8/-10 90	Version
Order No.	1497430000	cable lug, terminal end,10 mm ²
GTIN (EAN)	4050118306927	
Qty.	100 ST	

ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories

70 mm²70 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KWPN-M8/-70 90	Version	
Order No.	1497640000		cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307047		
Qty.	25 ST		
Type	KWPN-M10/-70 90	Version	
Order No.	1497650000		cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307177		
Qty.	25 ST		
Type	KWPN-M12/-70 90	Version	
Order No.	1497660000		cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307092		
Qty.	25 ST		
Type	KWPN-M16/-70 90	Version	
Order No.	1497680000		cable lug, terminal end,70 mm ²
GTIN (EAN)	4050118307122		
Qty.	25 ST		

10 mm²10 mm²

The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VPN/-10	Version	
Order No.	1498620000		cable lug, terminal end,10 mm ² ,10 mm ² ,None
GTIN (EAN)	4050118308136		
Qty.	100 ST		


ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

70 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VPN/-70	Version	
Order No.	1498670000	Version	cable lug, terminal end,70 mm ² ,70 mm ² ,None
GTIN (EAN)	4050118308020		
Qty.	50 ST		

10 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KQN-M4/-10	Version	
Order No.	1494010000	Version	cable lug, terminal end,10 mm ²
GTIN (EAN)	4050118303810		
Qty.	100 ST		
Type	KQN-M5/-10	Version	
Order No.	1494020000	Version	cable lug, terminal end,10 mm ²
GTIN (EAN)	4050118303681		
Qty.	100 ST		
Type	KQN-M6/-10	Version	
Order No.	1494030000	Version	cable lug, terminal end,10 mm ²
GTIN (EAN)	4050118303483		
Qty.	100 ST		
Type	KQN-M8/-10	Version	
Order No.	1494040000	Version	cable lug, terminal end,10 mm ²
GTIN (EAN)	4050118303803		
Qty.	100 ST		
Type	KQN-M10/-10	Version	
Order No.	1494050000	Version	cable lug, terminal end,10 mm ²
GTIN (EAN)	4050118303711		
Qty.	100 ST		

ES EPG 45 HEX 10/70


Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Type	KQN-M12/-10	Version	
Order No.	1494060000		cable lug, terminal end,10 mm²
GTIN (EAN)	4050118304008		
Qty.	100 ST		

70 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KQN-M6/-70	Version	
Order No.	1493190000		cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303261		
Qty.	50 ST		
Type	KQN-M8/-70	Version	
Order No.	1493210000		cable lug, terminal end,70 mm²
GTIN (EAN)	4050118302875		
Qty.	50 ST		
Type	KQN-M10/-70	Version	
Order No.	1493220000		cable lug, terminal end,70 mm²
GTIN (EAN)	4050118302882		
Qty.	50 ST		
Type	KQN-M12/-70	Version	
Order No.	1493230000		cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303032		
Qty.	50 ST		
Type	KQN-M16/-70	Version	
Order No.	1493240000		cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303131		
Qty.	50 ST		
Type	KQN-M20/-70	Version	
Order No.	1493250000		cable lug, terminal end,70 mm²
GTIN (EAN)	4050118303087		
Qty.	50 ST		


ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

10 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	KQNG-M5/-10	Version	
Order No.	1492680000		cable lug, terminal end, 10 mm ² , 10 mm ²
GTIN (EAN)	4050118302479		
Qty.	100 ST		
Type	KQNG-M6/-10	Version	
Order No.	1492690000		cable lug, terminal end, 10 mm ² , 10 mm ²
GTIN (EAN)	4050118302394		
Qty.	100 ST		
Type	KSN/-10	Version	
Order No.	1492780000		cable lug, terminal end, 10 mm ² , 10 mm ²
GTIN (EAN)	4050118302806		
Qty.	100 ST		
Type	VPLN/-10	Version	
Order No.	1492890000		cable lug, terminal end, 10 mm ² , 10 mm ² , None
GTIN (EAN)	4050118302561		
Qty.	100 ST		

70 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VPLN/-70	Version	
Order No.	1492940000		cable lug, terminal end, 70 mm ² , 70 mm ² , None
GTIN (EAN)	4050118302738		
Qty.	100 ST		


ES EPG 45 HEX 10/70

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

10 mm²



The use of insulated connectors guarantees users consistent electrical connection quality in the long term.

- Wide range of insulated and non-insulated cable lugs and connectors
- Tubular cable lugs according to current market standards (Euroseries)
- Compression cable lugs acc. to DIN 46235
- Sheet metal cable lugs acc. to DIN 46234
- Insulated ring cable lugs to DIN 46237
- Insulated pin cable lugs to DIN 46231

General ordering data

Type	VSTN/10	Version	
Order No.	1493030000		
GTIN (EAN)	4050118302776		
Qty.	100 ST		