

PEAN AL 95**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

We offer a broad portfolio of mounting support for easy handling and supplementation of our products. From various tools to insulating sleeves and various screws, our components are matched to each other down to the last detail and thus facilitate assembly in compliance with the respective standards and protective regulations.

General ordering data

Version	PE terminal, Screw connection, grey, 95 mm ² , Number of connections: 1, Steel
Order No.	1890720000
Type	PEAN AL 95
GTIN (EAN)	4032248500109
Qty.	5 items
Delivery status	Discontinued
Available until	2023-11-28T00:00:00+01:00

PEAN AL 95

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	24 mm	Depth (inches)	0.9449 inch
Height	75.7 mm	Height (inches)	2.9803 inch
Width	30 mm	Width (inches)	1.1811 inch
Net weight	105.8 g		

Temperatures

Ambient temperature	-5 °C...40 °C
---------------------	---------------

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	No SVHC above 0.1 wt%

Material data

Basic material	Steel	Colour	grey
----------------	-------	--------	------

System specifications

Version	PE terminal
---------	-------------

Additional technical data

Installation advice	Direct mounting
---------------------	-----------------

Conductors for clamping (rated connection)

Type of connection	Screw connection	Number of connections	1
--------------------	------------------	-----------------------	---

General

Installation advice	Direct mounting
---------------------	-----------------

Rating data

Rated cross-section	95 mm ²	Volume resistance according to IEC 60947-7-x	0.14 mΩ
Power loss in accordance with IEC 60947-7-x	7.42 W		

Classifications

ETIM 8.0	EC000901	ETIM 9.0	EC000901
ETIM 10.0	EC000901	ECLASS 14.0	27-25-01-03
ECLASS 15.0	27-25-01-03		