

SAI-ADAPT-M8/M8 4/3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



M8/M12 and M12/M8 adapters serve for quick implementation of the plug size.

General ordering data

Version	Y connector, M8 / M8
Order No.	1990570000
Type	SAI-ADAPT-M8/M8 4/3P
GTIN (EAN)	4050118376609
Qty.	1 items

SAI-ADAPT-M8/M8 4/3P

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS

Conform

Dimensions and weights

Net weight

10 g

Environmental Product Compliance

RoHS Compliance Status

Compliant with exemption

RoHS Exemption (if applicable/known)

6c

REACH SVHC

Lead 7439-92-1

SCIP

1c533b66-fcff-4da5-b89f-fd55fbf5cb55

Connection data

Single outlet 1 - plug-in connector

M8 pin

Single outlet 2 - plug-in connector

M8 socket

Tightening torque

M8: 0.5 Nm

Technical data customisable plug-in connectors

Number of poles

4

Coding

M8 = none

Nominal voltage

24 V

Nominal current

4 A

Protection degree

IP67

Pollution severity

3

Shield connection

No

Threaded ring material

Diecast zinc, nickel-plated

Temperature range of housing

-25...+85 °C

Standards

Connector standard

IEC 61076-2-104

General data

Number of poles

4

Coding

M8 = none

Connection thread

M8 / M8

Nominal voltage

24 V

Nominal current

4 A

Protection degree

IP67

Pollution severity

3

Shield connection

No

Temperature range of housing

-25...+85 °C

Conductor O.D.

-

Classifications

ETIM 8.0

EC002925

ETIM 9.0

EC002925

ETIM 10.0

EC002925

ECLASS 14.0

27-44-01-06

ECLASS 15.0

27-44-01-06


SAI-ADAPT-M8/M8 4/3P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing



Wiring diagram

