

## PAC-D15F-F-HF-4M

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



Similar to illustration

### General ordering data

|            |                                  |
|------------|----------------------------------|
|            |                                  |
| Order No.  | 2426030040                       |
| Type       | <a href="#">PAC-D15F-F-HF-4M</a> |
| GTIN (EAN) | 4099986598850                    |
| Qty.       | 1 items                          |

**PAC-D15F-F-HF-4M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)
**Technical data****Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Dimensions and weights**

|            |          |
|------------|----------|
| Net weight | 675.11 g |
|------------|----------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

**General Data**

|                       |                      |                     |                                          |
|-----------------------|----------------------|---------------------|------------------------------------------|
| Cable length          | 4 m                  | Suitable for        | Analogue signals                         |
| Cable                 | Cable LIHCH          | Interface connector | SUB-D FEMALE 15P                         |
| Number of poles, min. | 15-pole              | Connector PLC side  | H0.25/10 (FERRULES 0.25mm <sup>2</sup> ) |
| Wire cross-section    | 0.25 mm <sup>2</sup> |                     |                                          |

**Electrical Data**

|                          |                     |                                             |           |
|--------------------------|---------------------|---------------------------------------------|-----------|
| Total current, max.      | 3 A                 | Permissible current strength per path, max. | 1 A       |
| Rated voltage            | ≤ 60 Vdc ≤ 25 Vac   | Resistance                                  | ≤ 80 mΩ/m |
| Operating voltage        | ≤ 60 V DC ≤ 25 V AC | Capacity (wire / wires)                     | 300 pF/m  |
| Capacity (wire / shield) | 300 pF/m            |                                             |           |

**Rated data UL**

|                     |     |
|---------------------|-----|
| Total current, max. | 3 A |
|---------------------|-----|

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |