


**HDC MBUS 2 M MCLIP****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

**General ordering data**

|            |                                                                                        |
|------------|----------------------------------------------------------------------------------------|
| Version    | Data module, 0 V, Number of poles: 0, Crimp connection, Pin, Required plug-in slots: 1 |
| Order No.  | <a href="#">2667190000</a>                                                             |
| Type       | HDC MBUS 2 M MCLIP                                                                     |
| GTIN (EAN) | 4050118803877                                                                          |
| Qty.       | 1 items                                                                                |

## HDC MBUS 2 M MCLIP

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS

Conform

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Height     | 40.4 mm | Height (inches) | 1.5905 inch |
| Width      | 14.5 mm | Width (inches)  | 0.5709 inch |
| Net weight | 2.23 g  |                 |             |

## Temperatures

Limit temperature -40 °C ... 125 °C

## Environmental Product Compliance

|                        |                                                |
|------------------------|------------------------------------------------|
| RoHS Compliance Status | Compliant without exemption                    |
| REACH SVHC             | Potassium perfluorobutane sulfonate 29420-49-3 |
| SCIP                   | 1609748e-c278-4c9b-b3d1-e6215d2988cd           |

## General data

|                        |          |                              |                                       |
|------------------------|----------|------------------------------|---------------------------------------|
| Number of poles        | 0        | UL 94 flammability rating    | V-0                                   |
| Insulation resistance  | 1012 Ω   | Plugging cycles              | ≥ 500                                 |
| Type                   | Pin      | Surge voltage category       | III                                   |
| Pollution severity     | 3        | Basic material               | Polycarbonate, glass fibre reinforced |
| Series                 | ModuPlug | Rated voltage (DIN EN 61984) | 0 V                                   |
| Required plug-in slots | 1        |                              |                                       |

## PE connection data

|                    |                                   |
|--------------------|-----------------------------------|
| Connection type PE | Screw connection via module frame |
|--------------------|-----------------------------------|

## Version

|                    |                  |
|--------------------|------------------|
| Type of connection | Crimp connection |
|--------------------|------------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC002641    | ETIM 9.0    | EC002641    |
| ETIM 10.0   | EC002641    | ECLASS 14.0 | 27-44-03-12 |
| ECLASS 15.0 | 27-44-03-12 |             |             |

**HDC MBUS 2 M MCLIP**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

