

BIT E6.3 0.8X4.0X110

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



1/4" hexagon drive to DIN 3126, form E6.3 for direct machine connection

Slot-head bits DIN 5264, 1/4" drive, E6.3 DIN 3126

General ordering data

Version	Screwdriver insert, Blade width (B): 4 mm, Blade length: 110 mm, Blade thickness (A): 0.8 mm
Order No.	2749070000
Type	BIT E6.3 0.8X4.0X110
GTIN (EAN)	4050118895377
Qty.	5 items

BIT E6.3 0.8X4.0X110

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data**Approvals**

ROHS	Conform
------	---------

Dimensions and weights

Width	110 mm	Width (inches)	4.3307 inch
Net weight	10 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Bit with slotted blade, 0.5 x 3.0 x 110
------------------------	---

Screwing tools

Blade width (B)	4 mm	Blade thickness (A)	0.8 mm
Form	E 6.3 DIN 3126, Slotted	Blade length	110 mm

Classifications

ETIM 8.0	EC003864	ETIM 9.0	EC003864
ETIM 10.0	EC003864	ECLASS 14.0	21-04-42-04
ECLASS 15.0	21-04-42-04		