

SDIL 1,0X5,5X125**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Blade width (B): 5.5 mm, 125 mm, Blade thickness (A): 1 mm
Order No.	2749160000
Type	SDIL 1,0X5,5X125
GTIN (EAN)	4050118895469
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-28T00:00:00+01:00

SDIL 1,0X5,5X125

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data
Approvals

Approvals


Dimensions and weights

Width	280 mm	Width (inches)	11.0236 inch
Diameter	5.5 mm	Net weight	80.96 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 1.0x5.5x125	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	5.5 mm	Blade thickness (A)	1 mm
Form	Slotted	Blade length	125 mm

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		