

SDIL 1,2X6,5X150K**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

VDE insulated screwdriver sets, for working on live parts up to 1000 V AC and 1500 V DC, DIN EN 60900. IEC 900. Each piece is "GS" safety tested. Blade made from fully hardened, high-alloy chromium-vanadium-molybdenum steel, gun-metal finish.

General ordering data

Version	Screwdriver, Blade width (B): 6.5 mm, 150 mm, Blade thickness (A): 1.2 mm
Order No.	2749170000
Type	SDIL 1,2X6,5X150K
GTIN (EAN)	4050118895476
Qty.	1 items
Delivery status	This article will no longer be available in the future.
Available until	2026-02-28T00:00:00+01:00

SDIL 1,2X6,5X150K

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data**Approvals**

Approvals

**Dimensions and weights**

Width	305 mm	Width (inches)	12.0078 inch
Diameter	6.5 mm	Net weight	112 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	VDE-insulated screwdriver with slotted blade 1.2x6.5x150	Version	straight
------------------------	--	---------	----------

Screwing tools

Blade width (B)	6.5 mm	Blade thickness (A)	1.2 mm
Form	Slotted	Blade length	150 mm

Classifications

ETIM 8.0	EC000158	ETIM 9.0	EC000158
ETIM 10.0	EC000158	ECLASS 14.0	21-04-04-07
ECLASS 15.0	21-04-04-07		