

FP MONO K DC RC MF SP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Energy-efficient emergency lighting with a long service life

- developed and to be used in accordance with DIN EN 60598-2-22
- LED lamp for harsh environmental conditions (shocks and vibration, temperature range)
- higher energy efficiency and service life than fluorescent lamps
- Can be used worldwide thanks to the multi-voltage input (20 V...60 VDC)
- high fire protection classification V0
- Beam direction to one side
- 5W Power

Versions

- Pluggable with heavy duty connector and round connector
- Pre-assembled 2.5 mm²

General ordering data

Order No.	2815540000
Type	FP MONO K DC RC MF SP
GTIN (EAN)	4064675303633

FP MONO K DC RC MF SP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

UL File Number Search [UL Website](#)

Certificate no. (cULus) E345151

Dimensions and weights

Depth	104 mm	Depth (inches)	4.0945 inch
Height	61 mm	Height (inches)	2.4016 inch
Width	238 mm	Width (inches)	9.3701 inch
Net weight	590 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...55 °C
Humidity	92 % @ 25 °C		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1, Potassium perfluorobutane sulfonate 29420-49-3
SCIP	cfe9d4bf-2d88-4e4b-aa73-fe200a7615a0

General data

Silicone	No	Type of connection	Plug-in round connector with fixed number of poles
UL 94 flammability rating	V-0	Halogen	No
Type of mounting	Screw mounting	Nominal voltage	24 V
Protection degree	IP67	Surge voltage category	II
Pollution severity	2	Insulation voltage	<500 V (housing/PE)
Mounting position, installation notice	Arbitrary	Protection class	II
Amplitude of deflection	1.5 mm (2-9 Hz)	Vibration resistance EN 60721-3-3	Class 3M3 sinusoidal, stationary
Shock resistance EN 60721-3-3	Class 3M3 portable	Light current	454 lm
Connector cross-section, max.	2.5 mm ²	Connector cross-section, min.	0.5 mm ²
Altitude	≤ 3000 m	Short-circuit protection	Yes, internal
Light colour (CCT)	Cool White, 6000K, 6000K	Amplitude of acceleration	5 m/s ² (@ 9-200 Hz)
LED operating life	> 50.000 h	Shape of the LED module	Other
Efficiency class (according to EU Directive No. 874/2012)	Not required	Luminosity	3000 cd
Peak acceleration, type L	70 m/s ²		

Rated data acc. to IEC 60598-1

Power rating	5 W	Nominal current	20 mA
Input voltage	20...60 V DC	DC input voltage range	20...60 V DC

FP MONO K DC RC MF SP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Technical data****Classifications**

ETIM 8.0	EC000996	ETIM 9.0	EC000996
ETIM 10.0	EC000996	ECLASS 14.0	27-11-06-35
ECLASS 15.0	27-11-06-35		

Drawings

