

SD ELEC PRO**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Test instruments are indispensable when installing, servicing and repairing electrical systems and equipment. Weidmüller has a full range of test devices, including voltage testers, clamp-on meters and power socket/circuit-breaker testers. Weidmüller always takes into account the wishes and experience of users in its development and design work, which means that Weidmüller devices are tailored to the needs of practical applications and are extremely reliable.

General ordering data

Version	Voltage testers, No
Order No.	2855000000
Type	SD ELEC PRO
GTIN (EAN)	4064675530343
Qty.	1 items

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	22.2 mm	Depth (inches)	0.874 inch
Width	154.1 mm	Width (inches)	6.0669 inch
Length	154 mm	Length (inches)	6.063 inch
Diameter	22.2 mm	Net weight	29.92 g

Environmental Product Compliance

RoHS Compliance Status	Not affected
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Screwdriver Voltagetester
------------------------	---------------------------

Measuring and testing devices

Blade width (B)	3 mm	Load switchable	No
AC voltage measuring range	100-250 V	Working temperature, max.	50 °C
Working temperature, min.	-10 °C	Frequency range, max.	500 Hz
Frequency range, min.	50 Hz	Display	Visual
Blade length	63 mm	Phase sequence display	No
Continuity test	No	Test probe protection GS 38	No
Test probe illumination	No	HOLD function	No

Classifications

ETIM 8.0	EC000494	ETIM 9.0	EC000494
ETIM 10.0	EC000494	ECLASS 14.0	27-20-03-08
ECLASS 15.0	27-20-03-08		