

**THM WO 15/70 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

|            |                                 |
|------------|---------------------------------|
|            |                                 |
| Order No.  | 3034840000                      |
| Type       | <a href="#">THM WO 15/70 WS</a> |
| GTIN (EAN) | 4099986991729                   |
| Qty.       | 500 items                       |

## THM WO 15/70 WS

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Dimensions and weights

|            |         |                 |             |
|------------|---------|-----------------|-------------|
| Depth      | 0.03 mm | Depth (inches)  | 0.001 inch  |
| Height     | 15 mm   | Height (inches) | 0.5906 inch |
| Width      | 70 mm   | Width (inches)  | 2.7559 inch |
| Net weight | 112 g   |                 |             |

## General data

|                                   |                       |                                   |                |
|-----------------------------------|-----------------------|-----------------------------------|----------------|
| Adhesive                          | Polyacrylate adhesive | Type of printing                  | neutral        |
| Version                           | Self-adhesive         | Width                             | 70 mm          |
| UL 94 flammability rating         | V-0                   | Operating temperature range, max. | 150 °C         |
| Operating temperature range, min. | -40 °C                | Colour                            | white          |
| Halogen                           | No                    | Basic material                    | Polyester film |
| Printed characters                | without               | Size of labelling field           | 30 x 15 mm     |
| Approval acc. to UL 969           | Yes                   | Number per roll                   | 500            |

## Conductor and cable markers

|                               |                      |                               |                     |
|-------------------------------|----------------------|-------------------------------|---------------------|
| Halogen                       | No                   | Conductor cross-section, max. | 120 mm <sup>2</sup> |
| Conductor cross-section, min. | 0.75 mm <sup>2</sup> | Conductor O.D., max.          | 12.7 mm             |
| Conductor O.D., min.          | 9.6 mm               | Conductor O.D.                | 9.6 - 12.7 mm       |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC001530    | ETIM 9.0    | EC001530    |
| ETIM 10.0   | EC001530    | ECLASS 14.0 | 27-28-11-02 |
| ECLASS 15.0 | 27-28-11-02 |             |             |