

THM WO 25.4/95.2 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Order No.	3034870000
Type	THM WO 25.4/95.2 WS
GTIN (EAN)	4099986991750
Qty.	1000 items

THM WO 25.4/95.2 WS

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Approvals

ROHS	Conform
------	---------

Dimensions and weights

Depth	0.03 mm	Depth (inches)	0.001 inch
Height	25.4 mm	Height (inches)	1 inch
Width	95.2 mm	Width (inches)	3.748 inch
Net weight	421 g		

General data

Adhesive	Polyacrylate adhesive	Material colour according to resistance code	9
Type of printing	neutral	Version	Self-adhesive
Width	95.2 mm	UL 94 flammability rating	V-0
Operating temperature range, max.	150 °C	Operating temperature range, min.	-40 °C
Colour	white	Halogen	No
Basic material	Polyester film	Printed characters	without
Size of labelling field	25.4 x 25.4 mm	Approval acc. to UL 969	Yes
Number per roll	1000		

Conductor and cable markers

Halogen	No	Conductor cross-section, max.	400 mm ²
Conductor cross-section, min.	0.75 mm ²	Conductor O.D., max.	22.3 mm
Conductor O.D., min.	8.1 mm	Conductor O.D.	8.1 - 22.3 mm

Classifications

ETIM 8.0	EC001530	ETIM 9.0	EC001530
ETIM 10.0	EC001530	ECLASS 14.0	27-28-11-02
ECLASS 15.0	27-28-11-02		