

UC20-EM-232-485**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

General ordering data

Order No.	3042000000
Type	UC20-EM-232-485
GTIN (EAN)	4099987013352
Qty.	1 items

UC20-EM-232-485

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	66.5 mm	Depth (inches)	2.6181 inch
Height	40.5 mm	Height (inches)	1.5945 inch
Width	18.5 mm	Width (inches)	0.7283 inch
Net weight	0 g		

Connection data

Wire cross-section, solid, max. (AWG)	AWG 20	Wire cross-section, solid, min. (AWG)	AWG 16
Type of connection	PUSH IN	Wire cross-section, solid, max.	1.5 mm ²
Wire cross-section, solid, min.	0.14 mm ²		

Power supply

Supply voltage	5 V DC $\pm$ 4 % via UC20	Current consumption from Isys, typ.	<200 mA
----------------	---------------------------	-------------------------------------	---------

System data

Interface	RS232/485	Galvanic isolation	500 V DC
Connection type	PUSH IN		

Important note

Product information	The matching end brackets are included with the control.
---------------------	--

Classifications

ETIM 8.0	EC001423	ETIM 9.0	EC001423
ETIM 10.0	EC001423	ECLASS 14.0	27-24-22-08
ECLASS 15.0	27-24-22-08		

Accessories**BLF 3.50/180LR**

Connect efficiently - in a small space: female header with spring connection (PUSH IN) as a plug-in connection level; used together with male headers in 3.50 mm pitch.

General ordering data

Type	BLF 3.50/08/180LR SN OR...	Version
Order No.	2459740000	PCB plug-in connector, female plug, 3.50 mm, Number of poles:
GTIN (EAN)	4050118475159	8, 180°, PUSH IN with actuator, Conductor cross-section (rated
Qty.	48 ST	connection), max.: 1.5 mm², Box