

KLIPPON POK2 2M20AB CSS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Housing with threaded hole, 75 x 110 x 56.5, Glass fibre-reinforced polyester, Drill holes side A: 2 x M20x1.5, Drill holes side B: 2 x M20x1.5
Order No.	8000004161
Type	KLIPPON POK2 2M20AB CSS
GTIN (EAN)	4032248986187
Qty.	1 items

KLIPPON POK2 2M20AB CSS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technical data

Approvals

Approvals



ROHS Conform

Dimensions and weights

Depth	56.5 mm	Depth (inches)	2.2244 inch
Height	75 mm	Height (inches)	2.9527 inch
Width	110 mm	Width (inches)	4.3307 inch
Net weight	340 g		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1
SCIP	c0b142f1-4049-4b95-bbc3-9959a2d3b09c

Material data

Surface finish	untreated, polished	Basic material	Glass fibre-reinforced polyester
----------------	---------------------	----------------	----------------------------------

General data

Colour	Silver grey	Protection degree	IP66, IP67
Colour chart (similar)	RAL 7001		

Assembly properties

Adjacent	No
----------	----

Housing

Basic material	Glass fibre-reinforced polyester	Assembled to fit rail	
Drill holes side C	none	Drill holes side D	none
Drill holes side A	2 x M20x1.5	Unassembled to fit rail	TS15 98 KLIPPON POK2 CSS
Drill holes side B	2 x M20x1.5		

Standard features

Reference product	KLIPPON POK 081106
-------------------	------------------------------------

Classifications

ETIM 8.0	EC000261	ETIM 9.0	EC000261
ETIM 10.0	EC000261	ECLASS 14.0	27-18-01-01
ECLASS 15.0	27-18-01-01		

