

**KLIPPON POK51 4M20ABCSS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**General ordering data**

|            |                                                                                                                                                      |
|------------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| Version    | Housing with threaded hole, 160 x 160 x 91,<br>Glass fibre-reinforced polyester, Drill holes side A:<br>4 x M20x1.5, Drill holes side B: 4 x M20x1.5 |
| Order No.  | <a href="#">8000004164</a>                                                                                                                           |
| Type       | KLIPPON POK51 4M20ABCSS                                                                                                                              |
| GTIN (EAN) | 4032248986279                                                                                                                                        |
| Qty.       | 1 items                                                                                                                                              |

## KLIPPON POK51 4M20ABCSS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technical data

## Approvals

Approvals



ROHS Conform

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 91 mm  | Depth (inches)  | 3.5827 inch |
| Height     | 160 mm | Height (inches) | 6.2992 inch |
| Width      | 160 mm | Width (inches)  | 6.2992 inch |
| Net weight | 1302 g |                 |             |

## Environmental Product Compliance

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| RoHS Compliance Status               | Compliant with exemption             |
| RoHS Exemption (if applicable/known) | 6c                                   |
| REACH SVHC                           | Lead 7439-92-1                       |
| SCIP                                 | c0b142f1-4049-4b95-bbc3-9959a2d3b09c |

## Material data

|                |                     |                |                                  |
|----------------|---------------------|----------------|----------------------------------|
| Surface finish | untreated, polished | Basic material | Glass fibre-reinforced polyester |
|----------------|---------------------|----------------|----------------------------------|

## General data

|                        |             |                   |            |
|------------------------|-------------|-------------------|------------|
| Colour                 | Silver grey | Protection degree | IP66, IP67 |
| Colour chart (similar) | RAL 7001    |                   |            |

## Assembly properties

|          |    |
|----------|----|
| Adjacent | No |
|----------|----|

## Housing

|                    |                                  |                         |                                                                 |
|--------------------|----------------------------------|-------------------------|-----------------------------------------------------------------|
| Basic material     | Glass fibre-reinforced polyester | Assembled to fit rail   | <a href="#">KL SET 32W4 S</a> , <a href="#">KL SET 38Z2.5 S</a> |
| Drill holes side C | none                             | Drill holes side D      | none                                                            |
| Drill holes side A | 4 x M20x1.5                      | Unassembled to fit rail | <a href="#">TS35 POK51 SET</a>                                  |
| Drill holes side B | 4 x M20x1.5                      |                         |                                                                 |

## Standard features

|                   |                                    |
|-------------------|------------------------------------|
| Reference product | <a href="#">KLIPPON POK 161609</a> |
|-------------------|------------------------------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 8.0    | EC000261    | ETIM 9.0    | EC000261    |
| ETIM 10.0   | EC000261    | ECLASS 14.0 | 27-18-01-01 |
| ECLASS 15.0 | 27-18-01-01 |             |             |

**KLIPPON POK51 4M20ABCSS**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Drawings**

